

THRUST WASHERS

SHAFT SIZE	TYPE	MATERIAL
5 TO 25	HARDENED GROUND	STAINLESS STEEL DIN 1.4006 OR CARBON STEEL

STAINLESS STEEL STOCK NO.	CARBON STEEL STOCK NO.	INSIDE DIA. +0.30 -0.00	OUTSIDE DIA. +0.00 -0.31	T	Tolerance	SHAFT SIZE
CD1M-2-SS	CD1M-2	5.00	12.00	1.27	±0.05	5
CD1M-3-SS	CD1M-3	6.00	14.00			6
CD1M-4-SS	CD1M-4	7.00	17.00			7
CD1M-5-SS	CD1M-5	8.00	16.00			8
CD1M-6-SS	CD1M-6	10.00	21.00	1.57	+0.06 / -0.05	10
CD1M-7-SS	CD1M-7	12.00	24.00			12
CD1M-8-SS	CD1M-8	16.00	28.00	2.36	±0.08	16
CD1M-9-SS	CD1M-9	19.00	32.00			19
CD1M-10-SS	CD1M-10	25.00	41.00	3.18	+0.12 / -0.13	25

SHAFT SIZE	TYPE	MATERIAL
3 TO 25	PLASTIC	NYLON AND TEFLON

NYLON STOCK NO.	TEFLON® STOCK NO.	I.D. +0.13 -0.00	O.D. +0.00 -0.13	T ±.05	SHAFT SIZE
CD7M-1	CD8M-1	3.00	9	2.5	3
CD7M-2	CD8M-2	4.00	12	2.5	4
CD7M-3	CD8M-3	5.00	13	2.5	5
CD7M-4	CD8M-4	6.00	15	2.5	6
CD7M-5	CD8M-5	8.00	19	2.5	8
CD7M-6	CD8M-6	10.00	24	2.5	10
CD7M-7	CD8M-7	12.00	30	2.5	12
CD7M-8	CD8M-8	20.00	40	2.5	20
CD7M-9	CD8M-9	25.00	40	2.5	25

SHAFT SIZE	TYPE	MATERIAL
3 TO 11	LUBRICATING	BRONZE OIL-IMPREGNATED

STOCK NO.	I.D. +0.1 -0.0	O.D. +0.00 -0.1	T ±0.05	SHAFT SIZE
CD3M-1	3.1	8.9	1.5	3
CD3M-2	4.1	11.9	1.5	4
CD3M-3	6.1	14.9	1.5	6
CD3M-4	8.1	18.9	2.2	8
CD3M-5	10.1	23.9	3.0	10
CD3M-6	11.1	28.9	4.7	11

