




## Heyco® SunScreener® Wire Mesh Clip

- Helps protect solar panels from rodents and nesting birds with wire mesh screening (screening not included). See Heyco Sunscreen below.
- Constructed from 303 and 304 Stainless Steel for maximum endurance to outdoor elements.
- 303 Stainless Steel J-Hook easily attaches to the solar panel frames and can easily be trimmed or bent after assembly.
- 304 Stainless Steel Washers will firmly hold wire mesh screen to the module assembly preventing squirrels and rodents from damaging the interconnection wires and birds from building nests under the solar panel.
- Does not violate panel integrity.
- Installs quickly and easily with standard linesman pliers
- Black color available for those applications subject to **HOA appearance restrictions**.
- Stainless Steel Washers are offered in both steel color and black painted versions.
- Not for use in a marine salt water environment. Contact Heyco for alternative materials.
- DFARS Compliant

| PART NO.               |              | PART DIMENSIONS |       |          |     |       |     |        |     |                 |      |
|------------------------|--------------|-----------------|-------|----------|-----|-------|-----|--------|-----|-----------------|------|
| Steel                  | Gray         | A               |       | B        |     | C     |     | D      |     | E               |      |
|                        |              | Overall Length  |       | Diameter |     | Width |     | Height |     | Washer Diameter |      |
|                        |              | in.             | mm.   | in.      | mm. | in.   | mm. | in.    | mm. | in.             | mm.  |
| <b>Stainless Steel</b> |              |                 |       |          |     |       |     |        |     |                 |      |
| <b>S6437</b>           | <b>S6438</b> | 4.87            | 124,0 | .08      | 2,0 | .38   | 9,7 | .38    | 9,7 | 1.00            | 25,4 |




## Heyco® SunScreen™

Wire Mesh - For use with Heyco SunScreener Clips

| PART NO.     | PART DIMENSIONS |        |
|--------------|-----------------|--------|
|              | Width           | Length |
| Black        | in.             | feet   |
| <b>S6464</b> | 4               | 100'   |
| <b>S6466</b> | 6               | Rolls  |
| <b>S6468</b> | 8               |        |

- Mesh dimension is 1/2" x 1/2".
- DFARS Compliant
- For SunScreener Clips and SunScreen Mesh bundled in **Kit** form, see page 1-27.

*Quick Specs*



|          |                            |                     |
|----------|----------------------------|---------------------|
|          | SunScreener Wire Mesh Clip |                     |
| Material | J-Hook                     | 303 Stainless steel |
|          | Washer                     | 304 Stainless steel |

|  |  |
|--|--|
| SunScreen Wire Mesh                      |  |
| PVC Coated, galvanized welded steel mesh |  |