

Dependable protection, exceptional comfort and ease of use

3M™ Versaflo™ M-Series headgear for powered and supplied air respirators are lightweight, compact and easy to maintain while helping to provide the wearer with protection from a range of hazards. Their versatility and comfort help make them popular for many applications.



Directed airflow

A built-in air deflector allows users to direct the location of the airflow inside the headgear for increased control and comfort.

Modern, well-balanced, comfortable design

Versaflo™ M-Series headgear is lightweight, with excellent balance. The suspension includes six-point textile straps (four-point straps for 3M™ Versaflo™ M-206 Faceshield) for excellent comfort and weight distribution.

Coated visor with large viewing area

The visor design combines excellent peripheral and downward vision with good optical clarity. Coated visor option provides added chemical and scratch resistance in certain environments.



Easy maintenance

Easily removable parts allow simple cleaning, maintenance and replacement.

Easily adjustable suspension

Featuring an articulating ratchet suspension, M-Series products can be easily adjusted for the comfort of each individual user. The smooth ratchet mechanism allows for precise tightening control.

Versatility

To suit a wide range of needs, industries and applications, Versaflo™ M-Series headgear offer faceshields, covers and shrouds in a variety of fabrics. Accessories include earmuffs, peel-offs and a chin strap.

Parts and Accessories, *continued*

Breathing Tubes, Accessories and Adapters	Description	SKU (3M ID)	UPC Number
V-199	3M™ Adapter V-199/ 37069(AAD) 4/Case	70071042512	00051131370692
BT-20L	3M™ Versaflo™ Breathing Tube, BT-20L, Medium/Large, 1/case	70071533015	00051131373105
BT-20S	3M™ Versaflo™ Breathing Tube, BT-20S, Small/Medium, 1/case	70071533023	00051131373099
BT-922/W-3228-10	3M™ Versaflo™ Breathing Tube Cover BT-922 / W-3228-10, 10/case	78806025280	00051131373112
BT-30	3M™ Versaflo™ Length Adjusting Breathing Tube BT-30 1/case	70071563749	0005113173798
BT-40	3M™ Versaflo™ Heavy Duty Neoprene Rubber Breathing Tube BT-40 1/case	70071563756	00051131173804
BT-926/L-199SG	3M™ Versaflo™ High Temperature Breathing Tube Cover, Welding Safety BT-926/L-199SG 1 EA/Case	70071516556	00051135894514

Replacement Parts	Description	SKU (3M ID)	UPC Number
M-116	3M™ Versaflo™ Replacement Airflow Deflector M-116, for use with M-100 Faceshields 1/Case	70071544947	0005113173132
M-150	3M™ Versaflo™ Replacement Head Suspension M-150/ 37316(AAD) , for use with M-100 Faceshields 1/Case	70071544954	00051131373167
M-154	3M™ Versaflo™ Replacement Forehead Seal M-154, for use with M-100 Series Faceshields 1/Case	70071544962	0005113173149
M-170	3M™ Versaflo™ Faceshield Head Inserts M-170/ 37318(AAD) , for use with M-100 Faceshields 1 Pair/Case	70071544970	00051131373181
M-316	3M™ Versaflo™ Replacement Airflow Deflector M-316, for use with M-300 and M-400 Products 1/Case	70071562014	0005113173187
M-350	3M™ Versaflo™ Replacement Head Suspension M-350, for use with M-300 and M-400 Hardhats 1/Case	70071562022	00051131173194
M-354	3M™ Versaflo™ Replacement Forehead Seal M-354, for use with M-300 Hardhat 1/Case	70071562030	0005113173200
M-441	3M™ Versaflo™ Replacement Jaw Gasket M-441, for use with M-400 Helmets 1/Case	70071562071	00051131173248
M-935	3M™ Versaflo™ Standard Faceseal M-935/ 37325(AAD) 5/Case	70071562196	00051131373259
M-936	3M™ Versaflo™ Comfort Faceseal M-936/ 37326(AAD) 5/Case	70071562204	00051131373266
M-937	3M™ Versaflo™ Flame Resistant Faceseal M-937 5/Case	70071562212	0005113173316
M-956	3M™ Versaflo™ Size Reducing Ratchet Comfort Pad M-956/ 37327(AAD) 10/Case	70071562220	50051131373278
M-957/L-115	3M™ Versaflo™ Forehead Comfort Pad/Sweat Pad M-957/L-115/ 37010(AAD) 10/Case	70070798577	50051131370109
M-958/L-112	3M™ Versaflo™ Chin Strap M-958/L-112 2/Case	70070843340	50051138662566
M-960	3M™ Versaflo™ Replacement Visor Pivot Kit M-960 1 Pair/Case	70071562238	0005113173323
M-972	3M™ Versaflo™ Flame Resistant Headgear Cover M-972/ 37331(AAD) 1/Case	70071562246	00051131373310
M-976	3M™ Versaflo™ Head Neck and Shoulder Cover M-976/ 37332(AAD) , for use with M-100 and M-300 Products 1/Case	70071562253	00051131373327
M-985	3M™ Peltor™ Earmuff Assembly M-985/ 37333(AAD) , for Versaflo™ M-100 and M-300 Products 1 Pair/Case	70071562287	00051131373334

For more information

In U.S.

Technical Service
Hours of Operation: **1-800-243-4630**
8:00 a.m.–4:30 p.m. CST

Customer Care Center
Hours of Operation: **1-800-328-1667**
7:00 a.m.–5:00 p.m. CST

Internet
3M.com/WorkerSafety
3M.com/Versaflo

In Canada

Technical Service
Hours of Operation: **1-800-267-4414**
8:00 a.m.–4:30 p.m. EST

Customer Care
Hours of Operation: **1-800-364-3577**
7:30 a.m.–6:00 p.m. EST

Internet
3M.ca/safety



3M General Offices

3M Center, Building 235-2W-70
St. Paul, MN 55144-1000
3M.com
3M PSD products are for occupational use only.



WARNING

These respirators help protect against certain airborne contaminants. Before use, the wearer must read and understand the User Instructions provided as a part of the product packaging. A written respiratory protection program must be implemented meeting all the requirements of OSHA 1910.134, including training, fit testing and medical evaluation. In Canada, CSA standards Z94.4 requirements must be met and/or requirements of the applicable jurisdiction, as appropriate. Misuse may result in sickness or death. For correct use, consult packaging instructions and supervisor, or call 3M PSD Technical Service in USA at 1-800-243-4630 and in Canada at 1-800-267-4414.

3M, GVP, Speedglas, Versaflo and Vortemp are trademarks of 3M Company, used under license in Canada.

Please recycle. Printed in USA © 2015, 2017 3M. All rights reserved. 70-0715-7440-7 (rev5)