


A matched system of abrasives, tools and acces

In-Stock and Ready to Ship


- For dry-sanding composites, wood, metal, e-coats, gel coats, primer or almost any other substrate
- 3M™ Clean Sanding technology reduces dust more completely and efficiently
- Our most common clean sanding products are in stock and available for immediate shipping

3M™ Clean Sanding Discs and Sheets — Stock Products




216U

- Aluminum oxide mineral
- A weight, paper backing
- Load resistant coating
- Good value
- **Primary market:**
AOEM primer sanding




236U

- Aluminum oxide mineral
- C weight, paper backing
- Long life
- Load resistant coating
- **Primary markets:**
marine, metalworking and woodworking



360L

- Premium aluminum oxide mineral
- Film backing
- Excellent finish
- **Primary market:**
AOEM primer sanding



375L

- Premium aluminum oxide mineral
- Film backing
- Excellent finish
- **Primary markets:**
metalworking, woodworking, composites, paint finishing

	UPC			
Grade	3" Discs	5" Discs	6" Discs	3" x 4" Sheets
3M™ Clean Sanding Discs and Sheets 216U				
	100/inner — 500/case			
P220	051141-20830-5	051141-20538-0	Available only as KUT products.	Available only as KUT products.
P320	051141-20831-2	051141-20539-7		
P400	051141-20832-9	051141-20540-3		
P600	051141-20833-6	051141-20688-2		
P800	051141-27881-0	051141-27882-7		
3M™ Clean Sanding Discs and Sheets 236U				
	50/inner — 250/case			50/inner — 500/case
P80	051141-55517-1	051141-55598-0	051141-55506-5	051141-55534-8
P100	051141-55518-8	051141-55599-7	051141-55507-2	051141-55533-1
P120	051141-55519-5	051141-55600-0	051141-55508-9	051141-55532-4
P150	051141-55520-1	051141-55601-7	051141-55509-6	051141-55527-0
P180	051141-55521-8	051141-55500-3	051141-55510-2	051141-55528-7
P220	051141-55522-5	051141-55501-0	051141-55511-9	051141-55529-4
P240	051141-55523-2	051141-55502-7	051141-55512-6	—
P320	051141-55524-9	051141-55503-4	051141-55513-3	051141-55530-0
P400	051141-55525-6	051141-55504-1	051141-55514-0	051141-55531-7
P500	051141-55526-3	051141-55505-8	051141-55515-7	—
3M™ Clean Sanding Discs and Sheets 360L				
	100/inner — 500/case			
P220	051141-20821-3	051131-01704-7 051141-20541-0*	051141-20798-8	Available only as KUT products.
P240	051141-20822-0	051131-01705-4	051141-20799-5	
P280	051141-20823-7	051131-01706-1	051141-20800-8	
P320	051141-20824-4	051131-01707-8 051141-20542-7*	051141-20801-5	
P400	051141-20825-1 051141-20888-6*	051131-01708-5 051141-20543-4*	051141-20802-2	
P500	051141-20826-8 051141-20889-3*	051131-01709-2	051141-20803-9	
P600	051141-20827-5 051141-20891-6*	051131-01710-8	051141-20804-6	
P800	051141-20828-2 051141-20892-3*	051131-01711-5	051141-20805-3	
P1000	051141-20829-9	051131-01712-2	051141-20806-0	
3M™ Clean Sanding Discs 375L				
	50/inner — 250/case			
P60	—	051141-54029-0	051141-54036-8	—
P80	—	051141-54030-6	051141-54037-5	—
P100	—	051141-54031-3	051141-54038-2	—
P120	—	051141-54032-0	051141-54039-9	—
P150	—	051141-54033-7	051141-54040-5	—
P180	—	051141-54034-4	051141-54041-2	—
P220	—	051141-54035-1	051141-54042-9	—
P240	—	051141-54023-8	051141-54024-5	—
P280	—	051141-54043-6	051141-54044-3	—
P320	—	051141-54025-2	051141-54026-9	—
P400	—	051141-54027-6	051141-54028-3	—

*These products are shrink-wrapped with no inner boxes.