

Double Coated Polyethylene Foam Tape

3M™ Double Coated Polyethylene Foam Tape 4466W

- High-tack adhesive on a thick (1.6 mm) foam carrier formulated for many indoor general purpose mounting and joining applications
- Excellent for bonding to irregular surfaces by filling gaps
- Bonds to polyethylene, polypropylene, and many other plastics where moderate temperature and shear performance are required
- Distributes stress evenly over the bonded area
- Cushions and damps vibration, resists impact and provides insulating qualities
- 1/32 in, closed cell, polyethylene foam carrier with high tack rubber adhesive and 3 mil, densified kraft liner

UPC Code	Model	Size	Thickness	Color	Quantity
0 00 21200 24304 2	4466W	1/2 in x 36 yd	1/16 in	White	18/case
0 00 21200 24303 5	4466W	3/4 in x 36 yd	1/16 in	White	12/case
0 00 21200 24302 8	4466W	1 in x 36 yd	1/16 in	White	9/case
0 00 21200 30413 2	4466B	1/2 in x 36 yd	1/16 in	Black	18/case
0 00 21200 30412 5	4466B	3/4 in x 36 yd	1/16 in	Black	12/case
0 00 21200 30411 8	4466B	1 in x 36 yd	1/16 in	Black	9/case

3M™ Double Coated Polyethylene Foam Tape 4492W

- High shear acrylic adhesive on a 1.6 mm foam carrier formulated for more demanding indoor and moderate outdoor general purpose mounting and joining applications
- Temperature resistance of 158°F (70°C)
- Excellent for bonding to irregular surfaces by filling gaps
- Bonds to polyethylene, polypropylene, and many other plastics where moderate temperature and shear performance are required
- Distributes stress evenly over the bonded area
- Cushions and damps vibration, resists impact and provides insulating qualities 1/32 in, closed cell, polyethylene foam carrier with acrylic adhesive and a 4.0 mil, 58 lb polycoated kraft liner

UPC Code	Model	Size	Thickness	Color	Quantity
0 00 21200 24317 2	4492W	1/2 in x 72 yd	1/32 in	White	18/case
0 00 21200 24316 5	4492W	3/4 in x 72 yd	1/32 in	White	12/case
0 00 21200 24315 8	4492W	1 in x 72 yd	1/32 in	White	9/case
0 00 21200 30422 4	4492B	1/2 in x 72 yd	1/32 in	Black	18/case
0 00 21200 30421 7	4492B	3/4 in x 72 yd	1/32 in	Black	12/case
0 00 21200 30420 0	4492B	1 in x 72 yd	1/32 in	Black	9/case

To convert units of measure or performance, refer to the last page of this section.
The product calipers listed are nominal; please refer to specific product data pages for more detailed information.