

Catalog Number: TY5409
Product ID: 7TAG009550R0020
UPC Number: 78621080644
EAN Number: 05414363066385
Status: Active



Actual

Releasable Lashing Cable Tie, Black Polyamide (Nylon 6.6) for temperatures up to 85 Degrees Celsius (185 F), Weather Resistant for Indoor or Outdoor Applications, Length of 483mm (19.01 Inches), Width of 12.7mm (0.5 Inches), Thickness of 2mm (0.78 Inches), Tensile Strength Rating of 890 Newtons (200 Pounds), 25 Pack

North American Specifications (UNSPSC)

| | |
|------------------|------------------------------------|
| UNSPSC | 39121703 Cable ties |
| IGCC | 5045 Releasable Ties |
| Brand Name | Ty-Rap |
| Type | Lashing Tie |
| Width | 0.5 Inches/12.7mm |
| Length | 19.01 Inches/483mm |
| Thickness | 0.78 Inches/2.0mm |
| Bundle Diameter | 1.77 Inches/45mm-4.76 Inches/121mm |
| Material | Nylon/Polyamide 6.6 |
| Color | Natural |
| Lock Mechanism | Double Locking Head |
| Tensile Strength | 200 Pounds/890 Newtons |

European Specifications (ETIM)

| | |
|---------------------------|--------------------|
| ETIM | EC000046 Cable tie |
| Band width | 12.7mm |
| Length belt/tape/tie | 482.6mm |
| Max. bundle diameter | 120.65mm |
| Min. holding force | 889.6N |
| Model | Internal toothing |
| Band closure | Steel nose |
| Material | Plastic |
| Material quality | Polyamide PA |
| Surface protection | Untreated |
| UV-stable acc. ASTM D6779 | N |
| Halogen free | Y |
| Colour | Black |
| Transparent | N |
| Reflective (fluorescent) | N |
| Text strip | None |
| Solvable fastener | N |
| VG approval | N |
| MIL approval | N |
| UL approval | N |

Packaging

| | |
|---------------------------|------------------|
| Inner Quantity | 25 |
| Inner Dimensions (inches) | 27x6x0 |
| Outer Quantity | 250 |
| Outer Dimensions (inches) | 9.2x7.7x21.9 |
| Weight Uom | 3.5 lbs. per 100 |

Documents / Support Tools

| | |
|-------------------------|----------------------|
| Technical Data Sheet US | Available on Website |
| Technical Data Sheet CA | Available on Website |

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com