



Actual

Catalog Number: L-4-18-0-M
Product ID: 7TAG054070R0008
UPC Number: 72849491450
EAN Number: 05414363128410
Status: Active

Miniature Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 100.08mm (3.94 Inches), Width of 2.41mm (0.095 Inches), Thickness of 1.13mm (0.045 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

- Application Tools: ERG50, QC-100, L-200, L-400-C

North American Specifications (UNSPSC)

| | |
|------------------|---------------------------------------|
| UNSPSC | 39121703 Cable ties |
| IGCC | 5034 Cable ties |
| Brand Name | Catamount |
| Type | Minature |
| Standard | UL E49405 |
| Width | 0.095 Inch/2.41mm |
| Length | 3.94 Inches/100.08mm |
| Thickness | 0.045 Inch/1.13mm |
| Bundle Diameter | 0.0625 Inches/1.59mm-0.63 Inches/16mm |
| Material | Nylon/Polyamide 6.6 Weather Resistant |
| Color | Black |
| Lock Mechanism | Plastic Pawl |
| Tensile Strength | 18 Pounds/80 Newtons |

European Specifications (ETIM)

| | |
|--------------------------|--------------------|
| ETIM | EC000046 Cable tie |
| Band width | 2.41mm |
| Length belt/tape/tie | 100.08mm |
| Tie thickness | 1.13mm |
| Min. holding force | 80N |
| Model | Internal toothing |
| Band closure | Plastic lip/-cam |
| Material | Plastic |
| Material quality | Polyamide PA |
| Halogen free | Y |
| Colour | Black |
| Transparent | N |
| Reflective (fluorescent) | N |
| Text strip | None |
| Solvable fastener | N |

Packaging

| | |
|---------------------------|--------------------|
| Inner Quantity | 1000 |
| Inner Dimensions (inches) | 13x7x2 |
| Outer Quantity | 25000 |
| Outer Dimensions (inches) | 16.9x13.5x10.3 |
| Weight Uom | 0.66 lbs. per 1000 |

Documents / Support Tools

| | |
|-----------------------------|----------------------|
| Technical Data Sheet CA | Available on Website |
| Technical Data Sheet Global | wsd-000218 |

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com