

MACHINE SCREWS

THREAD	STYLE	MATERIAL
#000-120	BINDING, FLAT, ROUND AND FILLISTER	STAINLESS STEEL TYPE 18-8

HEAD STYLE				CLASS 2A THREAD	A LENGTH
BINDING STOCK NO.	FLAT STOCK NO.	ROUND STOCK NO.	FILLISTER STOCK NO.		
Y10-S000-A2	Y6-S000-A2	Y7-S000-A2	Y8-S000-A2	#000-120	1/8
Y10-S000-A3	Y6-S000-A3	Y7-S000-A3	Y8-S000-A3		3/16
Y10-S000-A4	Y6-S000-A4	Y7-S000-A4	Y8-S000-A4		1/4
Y10-S000-A5	Y6-S000-A5	Y7-S000-A5	Y8-S000-A5		5/16

THREAD	STYLE	MATERIAL
#00-96	BINDING, FLAT, ROUND AND FILLISTER	STAINLESS STEEL TYPE 18-8

HEAD STYLE				CLASS 2A THREAD	A LENGTH
BINDING STOCK NO.	FLAT STOCK NO.	ROUND STOCK NO.	FILLISTER STOCK NO.		
Y10-S00-A2	Y6-S00-A2	Y7-S00-A2	Y8-S00-A2	#00-96	1/8
Y10-S00-A3	Y6-S00-A3	Y7-S00-A3	Y8-S00-A3		3/16
Y10-S00-A4	Y6-S00-A4	Y7-S00-A4	Y8-S00-A4		1/4
Y10-S00-A5	Y6-S00-A5	Y7-S00-A5	Y8-S00-A5		5/16
Y10-S00-A6	Y6-S00-A6	Y7-S00-A6	Y8-S00-A6		3/8

THREAD	STYLE	MATERIAL
#0-80	SOCKET CAP, BINDING, BUTTON, FLAT, ROUND AND FILLISTER	STAINLESS STEEL TYPE 18-8

HEAD STYLE						CLASS 2A THREAD	A LENGTH
SOCKET CAP STOCK NO.	BINDING STOCK NO.	BUTTON STOCK NO.	FLAT STOCK NO.	ROUND STOCK NO.	FILLISTER STOCK NO.		
Y9-S0-A2	Y10S0-A2	Y19-S0-A2	Y6-S0-A2	Y7-S0-A2	Y8-S0-A2	#0-80	1/8
Y9-S0-A3	Y10S0-A3	Y19-S0-A3	Y6-S0-A3	Y7-S0-A3	Y8-S0-A3		3/16
Y9-S0-A4	Y10S0-A4	Y19-S0-A4	Y6-S0-A4	Y7-S0-A4	Y8-S0-A4		1/4
Y9-S0-A5	Y10S0-A5	Y19-S0-A5	Y6-S0-A5	Y7-S0-A5	Y8-S0-A5		5/16
Y9-S0-A6	Y10S0-A6	Y19-S0-A6	Y6-S0-A6	Y7-S0-A6	Y8-S0-A6		3/8
Y9-S0-A8	Y10S0-A8	Y19-S0-A8	Y6-S0-A8	Y7-S0-A8	Y8-S0-A8		1/2

THREAD	STYLE	MATERIAL
#2-56	SOCKET CAP, BINDING, BUTTON, FLAT, ROUND AND FILLISTER	STAINLESS STEEL TYPE 18-8

HEAD STYLE						CLASS 2A THREAD	A LENGTH
SOCKET CAP STOCK NO.	BINDING STOCK NO.	BUTTON STOCK NO.	FLAT STOCK NO.	ROUND STOCK NO.	FILLISTER STOCK NO.		
Y9-S2-A3	Y10-S2-A3	Y19-S2-A3	Y6-S2-A3	Y7-S2-A3	Y8-S2-A3	#2-56 UNC	3/16
Y9-S2-A4	Y10-S2-A4	Y19-S2-A4	Y6-S2-A4	Y7-S2-A4	Y8-S2-A4		1/4
Y9-S2-A5	Y10-S2-A5	Y19-S2-A5	Y6-S2-A5	Y7-S2-A5	Y8-S2-A5		5/16
Y9-S2-A6	Y10-S2-A6	Y19-S2-A6	Y6-S2-A6	Y7-S2-A6	Y8-S2-A6		3/8
Y9-S2-A8	Y10-S2-A8	Y19-S2-A8	Y6-S2-A8	Y7-S2-A8	Y8-S2-A8		1/2

