



New Vlier Glide Series light duty levelers, can be used on furniture, light duty machinery, tables, cabinets, and more.



- Low Cost
- 12 per package
- 10 new styles
- Popular inch & metric sizes

VG Series	THREAD	THREAD LENGTH	MAX LOADS lbs	PAD DIA mm (in)	PAD HT mm (in)
Part Number					
VGA24I625	1/4-20	25.0 (.98)	75	24.0 (.95)	8.0 (.32)
VGA24I820	5/16-18	20.0 (.79)			
VGA24M625	M6 x 1.0	25.0 (1.0)			
VGA24M822	M8 x 1.25	22.0 (.87)			
VGA38I623	1/4-20	28.0 (1.10)	100	36.6 (1.44)	8.5 (.34)
VGA38I827	5/16-18	27.0 (1.06)			
VGA38I925	3/8-16	25.0 (.98)			
VGA38M615	M6 x 1.0	15.0 (.59)			
VGA38M818	M8 x 1.25	18.0 (.71)	200	51.0 (2.0)	11.0 (.43)
VGA38M830		30.0 (1.18)			
VGB51A1960	3/8-16	60.0 (2.36)	200	51.0 (2.0)	11.0 (.43)
VGB51AM867	M8 x 1.25	67.0 (2.64)			
VGB51A1960-1	3/8-16	60.0 (2.36)			
VGB51AM867-1	M8 x 1.25	67.0 (2.64)			
VGC28I618	1/4-20	18.0 (.71)	80	28.0 (1.10)	14.5 (.57)
VGC28I625		25.0 (1.0)			
VGC28I818	5/16-18	18.0 (.71)			
VGC28I832		32.0 (1.26)			
VGC28M618	M6 x 1.0	18.0 (.71)	200	50.0 (1.97)	21.0 (.83)
VGC28M818	M8 x 1.25	18.0 (.71)			
VGC28M828		28.0 (1.10)			
VGC50AM1030	M10 x 1.5	30.0 (1.18)			
VGC50AM840	M8 x 1.25	40.0 (1.58)	100	31.3 (1.23)	14.2 (.56)
VGC50A11268	1/2-13	68.0 (2.68)			
VGD32I620	1/4-20	20.0 (.79)			
VGD32I540		40.0 (1.58)			
VGD32I820	5/16-18	20.0 (.79)			
VGD32I832		32.0 (1.26)			
VGD32I914	3/8-16	14.0 (.55)	100	31.3 (1.23)	14.2 (.56)
VGD32I934		34.0 (1.34)			
VGD32M615	M6 x 1.0	15.0 (.59)			
VGD32M630		30.0 (1.18)			
VGD32M815	M8 x 1.25	15.0 (.59)	100	29.0 (1.14)	14.0 (.55)
VGD32M830		30.0 (1.18)			
VGD32M1020	M10 x 1.5	20.0 (.79)			
VGD32M1030		30.0 (1.18)			
VGE29A1615	1/4-20	15.0 (.59)	100	29.0 (1.14)	14.0 (.55)
VGE29A1825	5/16-18	25.0 (.98)			
VGE29AM615	M6 x 1.0	15.0 (.59)			
VGE29AM815	M8 x 1.25	15.0 (.59)			

12 per package

**VLIER VLIER VLIER VLIER VLIER VLIER VLIER VLIER VLIER VLIER VLIER**

Call your Authorized VLIER dealer or contact us at 800/821-1090  
or visit us on the web at [www.vlier.com](http://www.vlier.com)





The NEW "VG" Series offers off the shelf ready to ship availability



VGF



VGH



VGJ



VGK



VGL

- Off the shelf availability
- Non marking pad material
- Protects floors
- Varied stud lengths for maximum height adjustment

VG Series	THREAD	THREAD LENGTH	MAX LOAD lbs	PAD DIA mm (in)	PAD HT mm (in)
<b>Part Number</b>					
VGF35I625	1/4-20	25.0 (.98)	200	35.0 (1.38)	13.0 (.51)
VGF35I630		30.0 (1.18)			
VGF35I815	5/16-18	15.0 (.59)			
VGF35I825		25.0 (.98)			
VGF35I915	3/8-16	15.0 (.59)			
VGF35I925		25.0 (.98)			
VGF35M615	M6 x 1.0	15.0 (.59)			
VGF35M630		30.0 (1.18)			
VGF35M820	M8 x 1.25	20.0 (.79)			
VGF35M830		30.0 (1.18)			
VGF35M1020	M10 x 1.5	20.0 (.79)	200	42.0 (1.65)	13.0 (.51)
VGF42I625	1/4-20	15.0 (.59)			
VGF42I630		30.0 (1.18)			
VGF42I825	5/16-18	25.0 (.98)			
VGF42I830		35.0 (1.38)			
VGF42I925	3/8-16	25.0 (.98)			
VGF42M815		15.0 (.59)			
VGF42M840	M8 x 1.25	40.0 (1.58)			
VGH50I815	5/8-18	15.0 (.59)	250	50.0 (1.97)	11.5 (.45)
VGH50I835		35.0 (1.38)			
VGH50I925	3/8-16	25.0 (.98)			
VGH50I950		50.0 (1.97)			
VGH50M815	M8 x 1.25	15.0 (.59)			
VGH50M840		40.0 (1.58)			
VGH50M1030	M10 x 1.5	30.0 (1.18)			
VGH50M1075		75.0 (2.95)			
VGJ29I825	5/16-18	25.0 (.98)	175	29.0 (1.14)	9.7 (.38)
VGJ29I925	3/8-16	25.0 (.98)			
VGJ29M820	M8 x 1.25	20.0 (.79)			
VGJ29M1030	M10 x 1.5	30.0 (1.18)	175	43.0 (1.69)	11.0 (.43)
VGJ43I835	5/16-18	35.0 (1.38)			
VGJ43I925	3/8-16	25.0 (.98)			
VGJ43M815	M8 x 1.25	15.0 (.59)			
VGJ43M1025	M10 x 1.5	25.0 (.98)	150	29.0 (1.14)	8.0 (.32)
VGK29I620	1/4-20	20.0 (.79)			
VGK29I625		25.0 (1.0)			
VGK29I825	5/16-18	25.0 (1.0)			
VGK29M625	M6 x 1.0	19.0 (.75)			
VGK29M819	M8 x 1.25	19.0 (.75)	175	43.0 (1.69)	11.0 (.43)
VGK35AI825	5/16-18	25.0 (1.0)			
VGK35AM625	M6 x 1.0	25.0 (1.0)			
VGK35AM825	M8 x 1.25	25.0 (1.0)			
VGL38I635	1/4-20	35.0 (1.38)	200	38.0 (1.18)	12.4 (.49)
VGL38I825	5/16-18	25.0 (.98)			
VGL38I915	3/8-16	15.0 (.59)			
VGL38M620	M6 x 1.0	20.0 (.79)			
VGL38M820	M8 x 1.25	20.0 (.79)			
VGL38M840		40.0 (1.58)			

12 per package

**VLIER Vlier Vlier Vlier Vlier Vlier Vlier Vlier Vlier Vlier Vlier**

Call your Authorized Vlier dealer or contact us at 800/821-1090  
or visit us on the web at [www.vlier.com](http://www.vlier.com)

