


SET SCREWS

THREAD	STYLE	MATERIAL
#0-80 TO 3/4-10	SLOTTED HEAD AND HEX SOCKET	STAINLESS STEEL 18-8 AND NYLON (SLOTTED HEAD ONLY)

SLOTTED HEAD STAINLESS STEEL	HEX SOCKET HEAD STAINLESS STEEL	SLOTTED HEAD NYLON	THREAD	L
STOCK NO.	STOCK NO.	STOCK NO.		
SC1-18	SC2-18	-	#0-80	1/8
SC1-19	SC2-19	-	#0-80	3/16
SC1-50	SC2-50	-	#2-56	3/32
SC1-1	SC2-1	-	#2-56	1/8
SC1-24	SC2-24	SC11-24	#2-56	3/16
-	SC2-25	SC11-25	#2-56	1/4
-	SC2-59	-	#2-64	1/16
SC1-14	SC2-14	-	#2-64	1/8
SC1-51	SC2-51	-	#4-40	3/32
SC1-2	SC2-2	-	#4-40	1/8
-	SC2-27	-	#4-40	3/16
-	SC2-28	SC11-28	#4-40	1/4
-	SC2-15	-	#5-40	3/16
-	SC2-52	-	#6-32	3/32
SC1-3	SC2-3	-	#6-32	1/8
-	SC2-30	SC11-30	#6-32	1/4
-	SC2-31	SC11-31	#6-32	3/8
-	SC2-32	SC11-32	#6-32	1/2
-	SC2-53	-	#8-32	1/8
SC1-4	SC2-4	-	#8-32	3/16
-	SC2-33	SC11-33	#8-32	1/4
SC1-54	-	SC11-54	#8-32	5/16
-	SC2-34	SC11-34	#8-32	3/8
-	SC2-35	SC11-35	#8-32	1/2
-	SC2-36	SC11-36	#8-32	5/8
-	SC2-16	-	#10-24	3/16
-	SC2-62	-	#10-24	1/4
SC1-60	SC2-60	SC11-60	#10-24	5/16
SC1-61	SC2-61	SC11-61	#10-24	3/8
SC1-5	SC2-5	-	#10-32	3/16
-	SC2-37	SC11-37	#10-32	1/4
SC1-55	SC2-55	SC11-55	#10-32	3/8
-	SC2-38	SC11-38	#10-32	1/2
-	SC2-39	-	#10-32	3/4
-	SC2-40	-	#10-32	1
-	SC2-41	SC 11-41	1/4-20	1/4
-	SC2-56	-	1/4-20	5/16
SC1-6	SC2-6	SC11-6	1/4-20	3/8
-	SC2-42	SC11-42	1/4-20	1/2
-	SC2-43	-	1/4-20	3/4
-	SC2-44	-	1/4-20	1
-	SC2-45	-	1/4-20	1-1/4
-	SC2-17	-	1/4-28	5/16
-	SC2-64	-	1/4-28	3/8
SC1-7	SC2-7	-	5/16-18	1/2
-	SC2-65	-	5/16-18	3/4
SC1-8	SC2-8	-	3/8-16	1/2
-	SC2-57	-	3/8-16	3/8
-	SC2-58	-	3/8-16	1/4
-	SC2-66	-	3/8-16	1
SC1-10	SC2-10	-	1/2-13	1/2
SC1-12	SC2-12	-	5/8-11	3/4
SC1-13	SC2-13	-	3/4-10	3/4



See Index for Allen Socket Head Keys.
These parts are sold in packages of 10.



Also available

STOCK NO.	DESCRIPTION OF KIT
KIT-SC2	STAINLESS HEX HEAD SET SCREWS #2 TO 1/4"
KIT-SCA	SET SCREWS - STAINLESS STEEL - CUP POINT AND SOFT TIP #0-80 TO 1/4"