

# SHOULDER SCREWS

THREAD	STYLE	MATERIAL
<b>#4-40 UNC-2A</b>	<b>HEX SOCKET HEAD</b>	<b>303 STAINLESS STEEL AND 416 STAINLESS STEEL HARDENED RC 26-36</b>

416 STAINLESS STEEL HARDENED RC 26-36	303 STAINLESS STEEL	THREAD	d +.000 -.001	L +.002 -.000	D	H	E	S
STOCK NO.	STOCK NO.							
PZ-1 PZ-2 PZ-3 PZ-4 PZ-5	PZ-1-3 PZ-2-3 PZ-3-3 PZ-4-3 PZ-5-3	#4-40 UNC-2A	.1245	.1255 .1880 .2505 .3130 .3755	1/4	1/8	5/32	5/64

THREAD	STYLE	MATERIAL
<b>#8-32 UNC-2A</b>	<b>HEX SOCKET HEAD</b>	<b>303 STAINLESS STEEL AND 416 STAINLESS STEEL HARDENED RC 26-36</b>

416 STAINLESS STEEL HARDENED RC 26-36	303 STAINLESS STEEL	THREAD	d +.000 -.001	L +.002 -.000	D	H	E	S
STOCK NO.	STOCK NO.							
PZ-6 PZ-7 PZ-8 PZ-9 PZ-10 PZ-11 PZ-12 PZ-13 PZ-14 PZ-15 PZ-16	PZ-6-3 PZ-7-3 PZ-8-3 PZ-9-3 PZ-10-3 PZ-11-3 PZ-12-3 PZ-13-3 PZ-14-3 PZ-15-3 PZ-16-3	#8-32 UNC-2A	.1870	.1255 .1880 .2505 .3130 .3755 .5005 .6255 .7505 1.0005 1.2505 1.5005	5/16	5/32	3/16	3/32

THREAD	STYLE	MATERIAL
<b>#10-32 UNC-2A</b>	<b>HEX SOCKET HEAD</b>	<b>303 STAINLESS STEEL AND 416 STAINLESS STEEL HARDENED RC 26-36</b>

416 STAINLESS STEEL HARDENED RC 26-36	303 STAINLESS STEEL	THREAD	d +.000 -.001	L +.002 -.000	D	H	E	S
STOCK NO.	STOCK NO.							
PZ-17 PZ-18 PZ-19 PZ-20 PZ-21 PZ-22 PZ-23 PZ-24 PZ-25 PZ-26 PZ-27	PZ-17-3 PZ-18-3 PZ-19-3 PZ-20-3 PZ-21-3 PZ-22-3 PZ-23-3 PZ-24-3 PZ-25-3 PZ-26-3 PZ-27-3	#10-32 UNF-2A	.2495	.1255 .1880 .2505 .3130 .3755 .5005 .6255 .7505 1.0005 1.2505 1.5005	3/8	3/16	1/4	1/8

