
MODEL 201



APPLICATIONS: EIA rack-mount chassis, tool boxes, industrial work stations, data processing, mechanical devices, point-of-purchase displays, and medical applications. Use model 201 whenever a light duty, 3/4 extension slide with positive stop is required.

Low Profile, Light Duty Slide 3/4 Extension Up to 108 lb. [49 kg.] Capacity*



Finish Bright electro-zinc (C)

- Length 12" to 28" [305mm to 711mm]
- Travel 3/4" length of slide
- Height 1.38" [35.1mm]

Load See chart *

Sidespace .38" + .030 / - .000 [9.6mm + 0.76 / - 0.00]

Mounting Side, bracket or hard mounting

Hardware #8 pan head screws

Features Positive stop


LUU					Luau rating	based on	sildes moun		wide drawe	i cycleu 10	,000 times.
Pa Num	-	Slide Length	Slide Travel	Load Rating lbs [kg] per pair *	А	В	С	D	E	F	G
201-	12	12.00 [305]	9.00 [229]	108 [49]		6.00 [152.4]	10.00 [254.0]		5.87 [149.1]	10.25 [360.4]	10.75 [273.1]
201-	14	14.00 [356]	11.00 [279]	103 [49]		8.00 [203.2]	12.00 [304.8]		7.87 [199.9]	12.25 [311.2]	12.75 [323.9]
201-1	16	16.00 [406]	12.00 [305]	95 [43]		10.00 [254.0]	14.00 [355.6]		9.87 [250.7]	14.25 [362.0]	14.75 [374.7]
201-1	18	18.00 [457]	13.00 [330]	90 [41]	8.00 [203.2]	12.00 [304.8]	16.00 [406.4]	8.37 [212.6]	11.87 [301.5]	16.25 [412.8]	16.75 [425.5]
201-2	20	20.00 [508]	15.00 [381]	82 [37]	9.00 [228.6]	14.00 [355.6]	18.00 [457.2]	9.37 [238.0]	13.87 [352.3]	18.25 [463.6]	18.75 [476.3]
201-2	22	22.00 [559]	16.00 [406]	75 [34]	10.00 [254.0]	16.00 [406.4]	20.00 [508.0]	10.37 [263.4]	15.87 [403.1]	20.25 [514.4]	20.75 [527.1]
201-2	24	24.00 [610]	17.00 [432]	67 [30]	11.00 [279.4]	18.00 [457.2]	22.00 [558.8]	11.37 [288.8]	17.87 [453.9]	22.25 [565.2]	22.75 [577.9]
201-2	26	26.00 [660]	19.00 [483]	60 [27]	12.00 [304.8]	20.00 [508.0]	24.00 [609.6]	12.37 [314.2]	19.87 [504.7]	24.25 [616.0]	24.75 [628.7]
201-2	28	28.00 [711]	20.00 [508]	55 [25]	13.00 [330.2]	22.00 [558.8]	26.00 [660.4]	13.37 [339.6]	21.87 [555.5]	26.25 [666.8]	26.75 [679.5]


* Load rating based on slides mounted in a 16" wide drawer cycled 10,000 times.

Installation Instructions

Instructions to Bracket Mount

- To ensure proper operation of the slides, make certain all mounting screws are inserted so the screw heads are inside the slides. (No washers on the inside of the slides.)
- 2. If sufficient space is available to install chassis from the rear of the rack, separate slide members (from the rear) for ease of installation. Otherwise, use access holes provided for mounting slide members to chassis and rack.
- 3. Using mounting kits and brackets, mount brackets to slide outer members (largest). For adjustment purposes screw the back brackets on loosely.
- 4. Install slides into EIA rack with #10-32 (customer supplied) screws and secure with bar nuts. Rear adjustment is possible by aligning the back bracket. Do not tighten screws until final adjustment is made.
- Mount slide inner members (smallest) to the chassis. Position inner members 1/8" [3.2mm] from the front edge of the chassis making sure both slides are parallel.
- 6. Check slide alignment by opening and closing the chassis. Any sign of binding indicates lateral stress or misalignment.
- 7. Adjust slide position until movement is smooth. Tighten all screws and if necessary use more to secure slides and complete installation.





Instructions to Hard Mount

- 1. Follow steps 1 & 2 of "Bracket Mount" instructions.
- Install slide outer members (largest) into cabinet using # 8 pan head screws. Be sure slides are parallel.
- Mount slide inner members (smallest) onto chassis. Leave all screws loose for future adjustment. Make sure slides are parallel.
- 4. Follow steps 6 & 7 of "Bracket Mount" instructions.

Slide Ordering Instructions

Complete your slide order for Model 201 by specifying the following:

	<u>10 Pair</u>	<u>C 201 -18</u>
Total Slides Required ——		
Slide Finish		
Slide Model		
Slide Length		
Optional Dolyhog Dookoging	(includes mountin	

Optional Polybag Packaging (includes mounting screws)-

Packaging

Distributor (D) Pack: All lengths are packaged 10 pair per box. Polybag includes one pair of slides and one screw hardware kit. Bracket kit ordered separately.

Bulk (P) Pack:	Lengths	12"–18"	25 pair per box
	Lengths	20"–22"	20 pair per box
	Lengths	24"–28"	10 pair per box

Order optional bracket mounting hardware kit (part number 4180-0222-XE) or bulk brackets and hardware kits separately.

Optional Hardware Kits

Optional mounting brackets are ordered as kits or bulk. Each kit contains enough brackets and hardware to mount one pair of slides. Order kit part number 4180-0222-XE.

	10 Each	4180-0222-XE
Total Bracket Kits Required —		
Optional Bracket Kit Part Number		

Bracket kit includes the following. See Figure 1.

4 short brackets (Part number 4000-0180-CE)

1 bracket hardware kit* (Part number 4180-0230-XE)

(*Kit contains screws, hex-nuts, washers, bar nuts)

For bulk, order 4 each short brackets and 1 hardware kit per pair of slides required. See Figure 2.

Total Brackets Required — Bracket Part Number ———	20 Each	4000-0180-CE
	5 Each	4180-0230-XE
Total Hardware Kits Required		
Hardware Kit* Part Number		

(*Kit contains screws, hex-nuts, washers, bar nuts.)

Specifications

Slide members: Cold rolled steel Ball retainers: Cold rolled steel Ball bearings: Carburized steel RoHs compliant

NOTE: Specifications, materials, prices, terms, and delivery are subject to change without notice.

ccuride

ACCURIDE INTERNATIONAL INC.

12311 Shoemaker Avenue Santa Fe Springs, CA 90670 TEL (562) 903-0200 FAX (562) 903-0208 www.accuride.com Manufacturing, Engineering, and Sales United States • Germany • Japan • Mexico • United Kingdom • China