


NOTE:

- 1.) ALL DIMENSIONS  
APPLY BEFORE PLATING
- 2.) THDS SHALL BE TO GAUGE FIT (BASIC) AFTER  
PLATING OR OTHER FINISH
- 3.) SURFACE SHALL BE SMOOTH, AND FREE OF TOOL MARKS
- 4.) BREAK ALL SHARP CORNERS AND REMOVE BURRS

REVISIONS			
SYM	DESCRIPTION	REVISED	DATE

FULL SECTION



STANDOFF		
PART NO.	LENGTH "A"	"C" NO. THDS
8248	.250	3-4
8249	.375	7-8
8250	.500	10-11
8251	.625	10-11
8252	.750	10-11
8253	.875	10-11
8254	1.000	10-11

MATERIAL: BRASS 360 1/2 HARD		FINISH: NICKEL	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		TITLE: 8248-8254	
.XX	.XX	.XXX	BRASS HEX
---	---	---	MALE/FEMALE STANDOFF
FRACTIONS	ANGLES	SCALE	
---	---	4X	
HEAT TREAT:		DRAWN: T. LORD	DATE: 12/6/03
		CHECKED: T. LORD	DATE: 12/6/03
PLOT SCALE:	1=1	APPROVED: T. LORD	DATE: 12/6/03
SIZE		DRAWING NUMBER	
B		SD: 8248-8254	
ISSUE		K	

**ABBATRON**  
Electronic Connectors and Hardware  
13680 S. MOSIERTOWN RD  
MEADVILLE, PA 16335