



MODEL 9308 LOCK-IN/LOCK-OUT


MODEL 9307 LOCK-OUT

APPLICATIONS: Designed for use in heavy-duty mobile and vehicular applications where a lock-in and lock-out are required. **This product is covered by U.S. and various foreign patents issued and/or pending.**

Extra Heavy-Duty, Full Extension
Up to 500 lb. [227 kg.] Load Rating
Optional Accessory Platform Brackets

- * Hole not available on the 9308-12 slide only
- o Hole not available on the 9308-22 only
- Available on 9308-48 and 9308-60 slides only
- △ Available on 9308-60 slides only
- Slide's lock-out for vertical mount only
- ◇ Depress lever to release slide from it's closed position, use the same lever to release the slide from it's locked out position

INCHES
[mm]



- Finish** Clear electroplate (C) only
- Length** Even lengths: 12"-36" [304.8 mm-914.4 mm] 40"-42" [1016 mm-1066.8 mm] 48"-60" [1219 mm-1524 mm]
- Travel** Full extension
- Height** 3.00" [76.2 mm]
- Side Space** .75" (+.031, -.000) [19.1 mm (+.79, -.00)]
- Movement** Steel ball bearings
- Load Rating**
 - Moderate Use 500 lbs. [227.3 kg.]
 - Frequent Use 400 lbs. [181.8 kg.]
 - Mobile (Vehicular) 300 lbs. [136.4 kg.]

- Mounting** Side mount **Only** (optional accessory platform brackets available)
- Features** Non-disconnect 9308 lock-in and lock-out. 9307 lock-out only. Bumper provides extra silencing during drawer closure.
- Companion** 9301 non-locking slide can be used in conjunction with locking 9307 or 9308 (see 9301 data sheet)
- Hardware** Customer supplied (see back page)

Caution: This slide must never be used as a pull-out step, platform, or any other application supporting human weight as injury may result.

Part Number	Slide Length	Slide Travel	A	B	C	D	E	F	G	H	J	K	M	N	P	Q	R
9308-12	12.00	12.00						6.06	7.06	7.81					8.00	10.25	11.00
	[304.8]	[304.8]						[153.9]	[179.3]	[198.4]					[203.2]	[260.4]	[279.4]
9308-14	14.00	14.00						8.06	9.06	9.81					10.00	12.25	13.00
	[355.6]	[355.6]						[204.7]	[230.1]	[249.2]					[254.0]	[311.2]	[330.2]
9308-16	16.00	16.00						10.06	11.06	11.81					12.00	14.25	15.00
	[406.4]	[406.4]						[255.5]	[280.9]	[299.9]					[304.8]	[361.9]	[381.0]
9308-18	18.00	18.00	5.00					12.06	13.06	13.81					14.00	16.25	17.00
	[457.2]	[457.2]	[127.0]					[306.3]	[331.7]	[350.8]					[355.6]	[412.8]	[431.8]
9308-20	20.00	20.00	5.00				11.69	14.06	15.06	15.81					16.00	18.25	19.00
	[508.0]	[508.0]	[127.0]				[296.9]	[357.1]	[382.5]	[401.6]					[406.4]	[463.6]	[482.6]
9308-22	22.00	22.00	5.00	7.50			13.69	16.06	17.06	17.81					18.00	20.25	21.00
	[558.8]	[558.8]	[127.0]	[190.5]			[347.7]	[407.9]	[433.3]	[452.4]					[457.2]	[514.4]	[533.4]
9308-24	24.00	24.00	5.00	7.50			15.69	18.06	19.06	19.81					20.00	22.25	23.00
	[609.6]	[609.6]	[127.0]	[190.5]			[398.5]	[458.7]	[484.1]	[503.2]					[508.0]	[565.2]	[584.2]
9308-26	26.00	26.00	5.00	7.50			17.69	20.06	21.06	21.81					22.00	24.25	25.00
	[660.4]	[660.4]	[127.0]	[190.5]			[449.3]	[509.5]	[534.9]	[553.9]					[558.8]	[615.9]	[635.0]
9308-28	28.00	28.00	5.00	7.50			19.69	22.06	23.06	23.81					24.00	26.25	27.00
	[711.2]	[711.2]	[127.0]	[190.5]			[500.1]	[560.3]	[585.7]	[604.8]					[609.6]	[666.8]	[685.8]
9308-30	30.00	30.00	5.00	7.50			21.69	24.06	25.06	25.81				9.25	19.75	26.00	28.25
	[762.0]	[762.0]	[127.0]	[190.5]			[550.9]	[611.1]	[636.5]	[655.6]				[234.9]	[501.6]	[660.4]	[717.6]
9308-32	32.00	32.00	5.00	7.50			23.69	26.06	27.06	27.81				9.25	21.75	28.00	30.25
	[812.8]	[812.8]	[127.0]	[190.5]			[601.7]	[661.9]	[687.3]	[706.4]				[234.9]	[552.5]	[711.2]	[768.4]
9308-34	34.00	34.00	5.00	7.50		20.50	25.69	28.06	29.06	29.81				9.25	23.75	30.00	32.25
	[863.6]	[863.6]	[127.0]	[190.5]		[520.7]	[652.5]	[712.7]	[738.1]	[757.1]				[234.9]	[603.2]	[762.0]	[819.1]
9308-36	36.00	36.00	5.00	7.50		20.50	27.69	30.06	31.06	31.81				9.25	25.75	32.00	34.25
	[914.4]	[914.4]	[127.0]	[190.5]		[520.7]	[703.3]	[763.5]	[788.9]	[807.9]				[234.9]	[654.1]	[812.8]	[869.9]
9308-40	40.00	40.00	5.00	7.50	14.50		31.69	34.06	35.06	35.81				9.25	29.75	36.00	38.25
	[1016.0]	[1016.0]	[127.0]	[190.5]	[368.3]		[804.9]	[865.1]	[890.5]	[909.5]				[234.9]	[755.6]	[914.4]	[971.5]
9308-42	42.00	42.00	5.00	7.50	14.50		33.69	36.06	37.06	37.81				9.25	31.75	38.00	40.25
	[1066.8]	[1066.8]	[127.0]	[190.5]	[368.3]		[855.7]	[915.9]	[941.3]	[960.4]				[234.9]	[806.5]	[965.2]	[1022.4]
9308-48	48.00	48.00	5.00	7.50	14.50	20.50	39.69	42.06	43.06	43.81				9.25	37.75	44.00	46.25
	[1219.2]	[1219.2]	[127.0]	[190.5]	[368.3]	[520.7]	[1008.1]	[1068.3]	[1093.7]	[1112.8]				[234.9]	[958.9]	[1117.6]	[1174.8]
9308-60	60.00	60.00	5.00	7.50	14.50	20.50	51.69	54.06	55.06	55.81				9.25	47.75	54.00	56.25
	[1524.0]	[1524.0]	[127.0]	[190.5]	[368.3]	[520.7]	[1312.9]	[1373.1]	[1398.5]	[1417.8]				[234.9]	[596.6]	[755.3]	[812.5]

* Load rating based on 18" slides mounted in a 32" wide drawer.

See 9301 technical sheet for further load information.

Mounting Instructions

1. With the slides fully extended, install cabinet member (outer member) with customer supplied 1/4" hex-head or pan head [M6 Euro] screws through the horizontal slots. Be sure slides are parallel.
2. Attach drawer to extended inner member with customer supplied 1/4" hex-head or pan head [M6 Euro] screws through the mounting holes/slots. Leave all screws loose for final adjustment. Adjust slide position until movement is smooth.
3. Tighten all screws and if necessary, use more screws to secure slides and complete installation. See Figure 1.

Customer Supplied Mounting Hardware

Metal Applications: 1/4" hex-head or pan head [M6 Euro] screw with .260 [6.6 mm] holes; **-or-** hex-head or pan head [M5 Euro] screw with .203 [5.2 mm] holes.

Wood Applications: 1/4" lag or sheet metal screw **-or-** #10 lag or sheet metal screw. Maximum screw head of .190 [4.8 mm] high by .500 [12.7 mm] diameter for clearance.

Optional Accessory Platform Brackets

Brackets provide four bottom-mount and two side-mount options. For bottom-mount, one bracket attaches to the slide outer member and the cabinet base. The other bracket attaches to the slide inner member and the platform or tray. For side-mount, the bracket attaches to the slide inner member.

See Figure 2 for examples of both mounting options. When the brackets are used either individually or in combination, they will accommodate all slide lengths. Each kit contains two brackets, four 1/4" hex-head screws, and four 1/4" hex nuts with lock washers. See separate Accessory Platform Bracket Kit data sheet for more information.

Slide Ordering Instructions

Locking Slide

The locking slide can be used on either the right hand side, left hand side, or both sides of the unit. After the length, specify "L" for left hand locking slide and "R" for right hand locking slide.

Complete your slide order for model 9308 or 9307 locking slide by specifying the following:

	4 Each	C	9308(07)	-22	-L	or
	4 Each	C	9308(07)	-22	-R	
Total Required Slides _____						
Slide Finish _____						
Locking Slide Model 9308 (07) _____						
Slide Length _____						
Locking Slide Hand _____						

NOTE: For applications requiring a lock on both sides, order an equal amount of "L" and "R" hand slides.



9301 Non-Locking Companion Slide

Model 9301 is unhandred and can be used on either the left or right hand side of the unit. For each locking slide ordered, order 1 companion slide.

Complete your slide order for model 9301 companion slide by specifying the following:

	4 Each	C	9301	-22
Total Required Slides _____				
Slide Finish _____				
Companion Slide Model 9301 _____				
Slide Length _____				

See 9301 technical sheet for additional information.



Packaging

Bulk Pack: Slides only. Left and right hand slides packaged in separate boxes.

Slide Lengths:	12" to 20"	8 each per box
	22" to 36"	4 each per box
	40", 42", 48", 60"	2 each per box

Specifications

Slide members: Cold rolled steel
Ball retainers: Polymer
Ball bearings: Carburized steel

Note: Specifications, materials, prices, terms, and delivery are subject to change without notice.

Accuride

ACCURIDE INTERNATIONAL INC.

12311 Shoemaker Avenue
Santa Fe Springs, CA 90670

TEL (562) 903-0200
FAX (562) 903-0208
www accuride.com

Manufacturing, Engineering, and Sales

United States • Germany • Japan • Mexico • United Kingdom • China