


APPLICATIONS: For use in wood pedestals, dresser and desk drawers, casework, residential and kitchen cabinetry. *Not intended for lateral file ❖ drawer applications.* Use for side mount only. **This product is covered by U.S. (5,980,007) and various foreign patents issued and/or pending.**

Vertical Drawer Adjustment
Self-Close Feature
Stay-Close Feature
Optional Face Frame Brackets



Finish Clear electroplate (C), black electroplate ⌘(CB), or white electrocoat ⌘(EW) finish

Length 3832CSC: 12" - 26" [300mm - 650mm]
3834CSC: 14" - 26" [350mm - 650mm]

Load 3832C slides rated at 100 lbs. ♦ [45.5 kg.] per pair
Rating 3834C slides rated at 90 lbs. ♦ [41.0 kg.] per pair

Travel 3832CSC: Full extension
3834CSC: 1" [25.4mm] over travel

Disconnect Handed lever disconnect

Height 1.80" [45.7mm]

Side Space .50" +0.031 / -0.0 [12.7mm +0.8 / -0.0]

Mounting Side, optional face frame brackets

Hardware Flat head 6mm Euro System screw or #8 pan head screw

Ball Bearings C & CB finish: Steel
EW finish: Acetal polymer in drawer member

Features Drawer member vertical cam adjustment; hold-in detent; silenced open and closed

NOTE: Drawer width should not exceed slide length.

NOTE: For optimal performance, make drawer 1-1/16" [27.0mm] less than cabinet opening.

NOTE: Slides may not function properly if side space is less than .50" [12.7mm].

❖ A lateral file drawer is wider than it is deep.

⌘ Minimum order quantities may apply.

♦ Load rating based on 18" slides mounted in a 16" wide drawer cycled 50,000 times.

Part Number	Slide Length	3832C SC Travel	3834C SC Travel	A	B	C	D	E	F
3832-C 12SC	11.81 [300]	11.25 [286]					9.09 [231]		
3832-C 14SC	13.78 [350]	14.00 [356]	15.00 [381]				11.06 [281]		
3832-C 16SC	15.75 [400]	16.00 [406]	17.00 [432]				13.03 [331]	11.34 [288]	
3832-C 18SC	17.72 [450]	18.00 [457]	19.00 [483]		12.60 [320]		14.99 [381]	12.60 [320]	
3832-C 20SC	19.69 [500]	20.00 [508]	21.00 [533]				16.96 [432]	15.12 [384]	
3832-C 22SC	21.65 [550]	22.00 [559]	23.00 [584]		16.38 [416]		18.93 [481]	16.38 [416]	
3832-C 24SC	23.62 [600]	24.00 [610]	25.00 [635]	8.82 [224]	16.38 [416]		20.90 [531]	13.86 [352]	18.90 [480]
3832-C 26SC	25.59 [650]	26.00 [660]	27.00 [686]	8.82 [224]	16.38 [416]	21.42 [544]	22.87 [581]	13.86 [352]	20.16 [512]



Installation Instructions

Install Cabinet Member


1. Separate slide members by simultaneously lifting up the left hand disconnect lever and pushing down the right hand lever.
2. Install cabinet (large) member first. For applications with an overlay drawer front, refer to Figure 1 for conventional mounting and Figure 2 for 32mm System mounting. For applications with an inset drawer front, set the slide back the thickness of the drawer front plus 1/8" [3.2mm].

Install Drawer Member

3. Install the drawer member with a screw through the cam adjuster and through a hole or slot at the rear.




4. Make sure the ball bearing retainers in the cabinet side are fully forward. Install drawer into cabinet. Close the drawer.
5. Open drawer and rotate the cam with a Phillips or Pozi screwdriver to vertically position the drawer in relation to the cabinet.



6. Install additional set screws to secure.

NOTE: Install drawer pulls or knobs **after** set screws are in place.



Slide Ordering Instructions

Complete your slide order for Accuride models 3832CSC or 3834CSC by specifying the following:

50 Pair C 3832 -C18 SC D

Total Required Slides _____

Slide Finish _____



Slide Model _____

Slide Length _____

Self-Close Feature _____

Polybag Packaging _____

Copyright © 2003 Accuride International Inc. Printed in U.S.A. 3700-1111(9466)-MK569-R1-0803




Optional Face Frame Brackets

Face frame brackets are ordered as a kit or in bulk. Brackets are available in clear zinc finish only. Mounting screws are not included.

To order kits, specify part number 4180-0322-XE. Each kit contains 2 front brackets, 2 rear brackets, and installation instructions. Order 1 kit per pair of slides.

For bulk, order 2 front brackets (P/N 4180-0516-CE) and 2 rear brackets (P/N 4080-0508-CE) per pair of slides.



Packaging

Distributor (D) Pack: All lengths are packaged 10 pair per box. Polybag includes one pair of slides with mounting screws.

Bulk (P) Pack: All lengths are packaged 10 pair per box. Slides and screws are ordered and packaged separately.

Specifications

Slide members and ball retainers: Cold rolled steel
Ball bearings: Carburized steel / acetal polymer

Note: Specifications, materials, prices, terms, and delivery are subject to change without notice.

Accuride

ACCURIDE INTERNATIONAL INC.

12311 Shoemaker Avenue
Santa Fe Springs, CA 90670

TEL (562) 903-0200

FAX (562) 903-0208

www accuride.com

Manufacturing, Engineering, and Sales

United States • Germany • Japan • Mexico • United Kingdom

Copyright © 2003 Accuride International Inc. Printed in U.S.A. 3700-9466(1111)-MK086-R1-0803