

Series 125 and 126 Retainers

WEIGHT

.40 g/cm (.036 oz/in)

MATERIALS AND FINISH

Material:

.41 (.016) thick Stainless Steel Type 301, Cond. 1/2 H, ASTM -A240

Finish:


Passivated per MIL-S-5002

SPRING RATE

60.4N/cm (34.5lbs/in) of deflection per spring finger

Dash No.	PCB Thickness	B Dimension +0.38 (.015) -0.0 (.000)	G Dimension +0.0 (.00) -0.80 (.03)
-06	1.6 (1/16)	1.91 (.075)	1.14 (.045)
-09	2.4 (3/32)	2.67 (.105)	1.91 (.075)

125 Shown, 126 Opposite



Part Number Code

PCB Thickness

1.6 (.063) 06
2.4 (.094) 09

Length

31.75 (1.25) to 311.15 (12.25) 3.25
in 25.4 (1.00) increments
Other lengths available on request

125 or 126 -06 - 3.25

Part Number Code Example:

125-06-4.25

Series 125 passivated stainless steel, 107.95 (4.25) long designed for 1.6 (.063) thick printed circuit boards

