

Series NW125 and NW126 Retainers

WEIGHT

.32 g/cm (.029 oz/inch)

MATERIALS AND FINISH

Material:

.41 (.016) thick Stainless Steel Type 301, Cond. 1/2 H, ASTM -A240

Finish:

Passivated per MIL-S-5002

SPRING RATE

60.4N/cm (34.5lbs/in) of deflection per spring finger


Part Number Code

PCB Thickness		NW125 or NW126	-06	-3.25
1.6 (.063)			06	
2.4 (.094)			09	
Length		31.75 (1.25) to 311.15 (12.25)		3.25
in 25.4 (1.00) increments				
Other lengths available on request				

Part Number Code Example:

NW125-06-4.25

Series NW125 passivated stainless steel, 107.95 (4.25) long designed for 1.6 (.063) thick printed circuit boards



Dash No.	PCB Thickness	B Dimension + 0.38 (.015) - 0.0 (.000)	G Dimension + .254 (.010) - .254 (.010)
-06	1.6 (1/16)	2.41 (.095)	3.56 (.140)
-09	2.4 (3/32)	1.65 (.065)	2.80 (.110)

NW125 Shown, NW126 Opposite

