

ACCESSORIES

Dynabrade Air Lube

10W/NR

- Formulated for pneumatic equipment.
- Absorbs up to 10% of its weight in water.
- Prevents rust and formation of gum/sludge for longer tool operation with greater power and less downtime.

MODEL 95821

4 oz. (118 ml)

MODEL 95843

1 gal. (3.8 l)

MODEL 95842

1 pt. (473 ml)

IMPORTANT: General air tool maintenance begins with motor lubrication. Filter-regulator-lubricators are also necessary for greater performance and increased life of air tools. Dynabrade tools must be used with filter-regulator-lubricators to maintain all warranties.



Oil Gun

95541

Push-type Oil (one-hand operation)



Gear Oil

MODEL 95848

2.5 oz. (74 ml) tube

- Formulated for Dynabrade geared tools utilizing a wick-type lubrication system. Apply every 8 hours of operation into tools lubrication fitting.
- For use with our sander/polishers, disc sanders, die grinders and depressed center wheel grinders.
- Failure to lubricate will cause premature gear failure and void warranty.
- Easy to apply using with Dynabrade P/N 95541 Oil Gun (shown, sold separately).



Dynuba®

Cleaning and Polishing Products for Abrasive and Polishing Belts

Ozone Safe!

- Our most popular Dynuba product.
- Keeps belts free of metal build-up when sanding non-ferrous metals with grit 80 or finer.
- Extends belt life.

MODEL 60000

- 11.25 oz. can.

MODEL 60001

- 1-gal. can.

MODEL 60003

- 5-gal. can.

MODEL 60004

- 55-gal. drum.



Grease

MODEL 95542

10 oz. (283.5 g) Tube

- Multi-purpose grease for all types of bearings, cams, gears.
- High film strength; excellent resistance to water, steam, etc.
- Workable range 0° F to 300° F.



Dynacushion® Abrasive Belts

These abrasive belts cut faster and last longer than most coated abrasive products when grinding steel or stainless steel with Dynabrade small belt tools. The belts are very sharp and are excellent for use on most metals including aluminum and titanium when lubricated properly.



COATED ABRASIVE DYNACUT BELTS


- 15-1/2" (394 mm) Long



Belt Width Inch (mm)	Abrasive Grit					
	60	80	120	180	220	320
3-1/2 (89)	90272	90273	90275	90277	90338	90339

3M SCOTCH-BRITE® ABRASIVE IMPREGNATED NON-WOVEN NYLON BELTS

- 15-1/2" (394 mm) Long



Belt Width Inch (mm)	Abrasive Grade/Grit Equivalent					
	Type T Polishing	Super Fine Grey (320-600)	Very Fine Blue (220-320)	Medium Maroon (150-180)	Coarse Brown (80-150)	SE Coarse
3-1/2 (89)	90051	90014	90281	90282	90283	90278