



Random Orbital Sanding Pads

Dynabrade exclusive single-piece hub design!

Premium urethane sanding pads are perfectly weight-mated to Dynabrade tools, for achieving consistent swirl-free finishes



Non-Vacuum



Vacuum - 5 Hole



Vacuum - 44 Hole



	Part No.	Type	Holes	Face	Nap	Thickness	Density
5" (127 mm)	56106	Non-Vacuum	-	Vinyl-Face	-	3/8" (10 mm)	Medium
	54325			Hook-Face			
	56104	Vacuum	5	Vinyl-Face	Short	3/8" (10 mm)	Medium
	54326			Hook-Face			
	56320		44				
6" (172 mm)	56321	Vacuum	52	Hook-Face	Short	3/8" (10 mm)	Medium

Dynaline Sanding Pads

Premium urethane

Mounts to Dynaline with two screws



	Part No.	Type	Face	Nap	Thickness	Density
2-3/4" x 8" (70 mm x 203 mm)	57454	Non-Vacuum	Vinyl-Face	-	3/8" (10 mm)	Medium
3-2/3" x 7" (93 mm x 178 mm)	57851	Non-Vacuum	Hook-Face	Short	3/8" (10 mm)	Medium
	57852			Long		

Thermoplastic Pads

Fins help expel heat from disc pad extending disc life

Accepts abrasive discs with 7/8" (22 mm) center hole includes flange nut



	Part No.	Center Hole	Max. RPM	Density
4-1/2" (114 mm)	50288	5/8" Diameter	13,000	Medium
5" (127 mm)	51150		12,000	

Rubber Molded Pads

Spiral ribs form air-flow channels, extending disc life

Accepts abrasive discs with 7/8" (22 mm) center hole, includes flange nut



	Part No.	Thread	Max. RPM	Density
4-1/2" (114 mm)	50281	5/8"-11 Female	13,500	Medium
5" (127 mm)	50282		15,000	
7" (178 mm)	50283		8,600	

Sanding Pads for Locking-Type Discs

(2) Female threaded options

Includes Pad Adapter (50103) to convert 1/4"-20 female thread to 1/4" dia. shank



	Part No.	Thread	Max. RPM	Density
2" (51 mm)	51344	1/4"-20	30,000	Medium
	51345	3/8"-24		
3" (76 mm)	51346	1/4"-20	20,000	
	51347	3/8"-24		