

### Dynaswivel® Air Line Connectors

Never fight an air tool again!

- Two pivot points that swivel 360° dropping air hose directly to floor
- Improve tool maneuverability and minimize operator fatigue

Composite – non-marring construction

Aluminum and Stainless Steel – durable metal construction

Flow Control – finger-tip air-flow control dial



	Part No.	Thread	Style	Air Flow
Composite	94300	1/4" NPT	Standard	up to 33 SCFM (935 LPM)
	94407		Flow Control	up to 46 SCFM (1,303 LPM)
Aluminum & Stainless Steel	95460	1/4" NPT	Standard	up to 25 SCFM (708 LPM)
	95461	3/8" NPT		up to 45 SCFM (1,275 LPM)
	95462	1/2" NPT		up to 65 SCFM (1,841 LPM)
	95734	1/4" NPT	Flow Control	up to 25 SCFM (708 LPM)

### Coupler/Plug Assemblies

Plugs with steel and brass couplers

- Includes one female coupler and one male plug
- Maximum working pressure: 150 PSIG (10 Bar)
- Temperature Range: -4° F – 212° F



	Part No.	Coupler	Plug	Air Flow
1/4" NPT	95676	Female	Male	up to 74 SCFM (2,095 LPM)
3/8" NPT	98265			up to 138 SCFM (3,900 LPM)
1/2" NPT	98273			

### Dynabrade Air Lube (10W/NR)

Formulated for pneumatic equipment

- Absorbs up to 10% of its weight in water
- Prevents rust and formation of gum/sludge for longer tool operation with greater power and less downtime

4 oz. (118 ml) Part No. 95841

1 pt. (473 ml) Part No. 95842



### Grease and Grease Gun

Workable temperature range 0° – 300° F

- High film strength; excellent resistance to water, steam, etc
- Multi-purpose grease for all types of bearings, cams, gears
- Push-type gun for one-hand operation

2.5 oz. (74 ml) Part No. 95544

Grease Gun Part No. 95541



### Gear Oil and Oil Gun

For Dynabrade Wick Lube System

- Apply every 8 hours of operation
- Push-type gun for one-hand operation

2.5 oz. (74 ml) Part No. 95848

Oil Gun Part No. 95541

