



Paper sheets and rolls are engineered for optimum performance when sanding metal, wood, composites and painted surfaces. The sheets are packed in protective packaging to eliminate waste and permit easy, neat storage.

Categories: All purpose, wood sanding, stearted (non-loading), waterproof, and heavyweight

Applications: Light-duty metal sanding, primer sanding, defect removal from painted surfaces, filler sanding, sanding and finishing of composites and fiberglass, bare wood sanding, sanding between sealer coats

Size Range: Full Sheets, Cut Sheets, File Strips and Rolls

Grit Range: 36 – 2500

Abrasive Grain: Ceramic Alumina, Zirconia Alumina, Aluminum Oxide, Silicon Carbide, and Garnet

Paper Weights: Heavyweight – E; Lightweight – A and D

Machine Used:



MATERIAL-TO-PRODUCT RECOMMENDATION GUIDE

	BEST Highest Productivity – Lowest Total Cost	BETTER Excellent Blend of Performance & Price	GOOD Consistent Performance – Low Initial Price
Unfinished Metal	Original Performance A275	–	Gold Reserve A296, PB273
Primed / Painted Surfaces / Between Coats	Original Performance A275	Durite A475	Gold Reserve A296, PB273
Fiberglass / Composites	Original Performance A275	Durite A475	Gold Reserve A296, PB273
Bare Wood	Original Performance A275	–	Garnet A511, Garnet A513, Garnet A514
Clear Coat Sanding	Black Ice T214, Black Ice T401	–	TufBak T461
Sealer Sanding	Original Performance A275	Durite A475	Gold Reserve A296, PB273
Lacquer Sanding	Black Ice T214, Black Ice T401	Blue-Bak T414	TufBak T461
Wet Sanding	Black Ice T214, Black Ice T401	Blue-Bak T414	TufBak T461
Paint Stripping	Original Performance A275, ProSand A259PS	Durite A475	A290
All Purpose Dry Sanding	Original Performance A275, ProSand A259PS	–	A212, A213, A211

APPLICATION/GRIT RECOMMENDATION GUIDE

COARSER (STOCK REMOVAL)										FINER (FINISHING)											
36	40	60	80	100	120	150	180	220	240	280	320	360	400	500	600	800	1000	1200	1500	2000	2500
Roughing to Intermediate				Intermediate to Finishing										Fine Finishing							
										Ultra Fine Finishing											

RECOMMENDED BACKING WEIGHT

	H-WT	F-WT	E-WT	D-WT	C-WT	B-WT	A-WT	
Stiffest / Strongest Most Aggressive Applications								Most Flexible / Lightest Applications

Hand Sanding Cut Sheets

Paper Cut Sheets



TIER:	GOOD	GOOD
BRAND:	Norton	Norton
TRADENAME:	A290 NO-FIL	A213
ABRASIVE:	Aluminum Oxide	Aluminum Oxide
BACKING WEIGHT:	C-Weight	C-Weight
OTHER:	P-Graded	P-Graded

SIZE (W x L)	GRIT	MIN./STD. PKG.	PART #	PART #
3-2/3 x 9	60	100/1000		66261102925
	80	100/1000	66261101119	66261102920
	100	100/1000		66261102900
	120	100/1000		66261102895
	180	100/1000	66261101124	
	220	100/1000	66261101123	

Rubber Hand Sanding Blocks

- Resilient rubber blocks that conform well to mild contours and flat surfaces



DESCRIPTION	STD. PKG.	PART #
2-3/4 x 5	5	07660701889

PSA Rolls

PSA (Pressure Sensitive Adhesive) Paper Rolls



TIER:	BEST	BEST	BEST	BETTER	BETTER	BETTER	BETTER	GOOD
BRAND:	Norton	Norton	Norton	Norton	Norton	Norton	Norton	Norton
TRADENAME:	DRY ICE A975 NO-FIL	DRY ICE A975 NO-FIL	DRY ICE A975 NO-FIL	OP A275 NO-FIL	OP A275 NO-FIL	OP A275 NO-FIL	OP A275 NO-FIL	GOLD RESERVE A296 NO-FIL
ABRASIVE:	Ceramic Alumina	Ceramic Alumina	Ceramic Alumina	Aluminum Oxide	Aluminum Oxide	Aluminum Oxide	Aluminum Oxide	Aluminum Oxide
BACKING WEIGHT:	C-Weight.	C-Weight.	B-Weight.	B-Weight.	B-Weight.	B-Weight.	B-Weight.	B-Weight
BACKING ATTACHMENT:	PSA	PSA	PSA	PSA	PSA	PSA	PSA	PSA
OTHER:	P-Graded	P-Graded	P-Graded	P-Graded	P-Graded	P-Graded	P-Graded	P-Graded
SIZE:	2-3/4" x 25 yd	2-3/4" x 30 yd	2-3/4" x 45 yd	2-3/4" x 25 yd	2-3/4" x 30 yd	2-3/4" x 45 yd	4-1/2 x 10 yd	2-3/4" x 25 yd

GRIT	MIN./STD. PKG.	PART #	PART #	PART #	PART #	PART #	PART #	PART #
80	1/5	66261149566			66261131691			66261131697
100	1/5					66261131690		66261131696
120	1/5		66261149564			66261131689		66261131695
150	1/5			66261149563			66261131688	66261131694
180	1/5			66261149562			66261131687	66261131693
220	1/5			66261149561			66261131686	66261131692
240	1/5						66261131685	
320	1/5			66261149558			66261131683	
400	1/5			66261149557			66261131681	
500								
600	1/5						66261131679	