


Cable Ties



Panduit® offers the most complete selection of cable tie styles, sizes, materials and colors to meet our customers' needs. Panduit cable ties bundle, mount, and identify in countless indoor, outdoor, and harsh environment applications. Panduit cable ties, wiring accessories, and installation tools allow our customers to achieve the lowest total installed cost of managing wire and cable.



- Panduit continues to provide innovative new cable tie designs to meet our customers' application challenges
- Panduit cable ties and wiring accessories can be used in a variety of applications and environments, providing the optimal wire management solution
- Panduit offers a large selection of ergonomic cable tie installation tools – all with consistent, and reliable performance

Panduit leads the industry in the breadth and depth of available cable tie designs created from customer feedback on their application requirements. As with all Panduit products, quality in design and production along with customer service excellence are assured.

Features and Benefits – Sta-Strap® Cable Ties

Two-piece design incorporates a separate nylon head and strap.

B1.
Cable
Ties

B2.
Cable
Accessories

B3.
Stainless
Steel Cable
Ties &
Accessories

C1.
Wiring
Duct

C2.
Abrasion
Protection

C3.
Cable
Management

D1.
Terminals

D2.
Power
Connectors

D3.
Grounding
Connectors

E1.
Labeling
Systems

E2.
Labels


E3.
Pre-Printed
&
Write-On
Markers

E4.
Permanent
Identification

E5.
Industrial
Safety
Solutions

F.
Keystone
Cabling
Systems

G.
Part
Number
Index



Cable tie tools speed installation and reduce total installed cost. Visit www.panduit.com/tools.



Cable tie accessories are used to speed and simplify the mounting of wires, cables, and tubing. See pages B2.1 – B2.26.



Material, Color (Suffix)	Style/Function	Part Number Prefix	Catalog Page
Nylon 6.6, Natural (No Suffix)	Locking Ties/Bundle	SST	B1.65
	Clamp Ties/Mount	SSC	B1.67
	Marker Ties/Identify	SSM	B1.68
Weather Resistant Nylon 6.6, Black (0)	Locking Ties/Bundle	SST	B1.66
	Clamp Ties/Mount	SSC	B1.67
	Marker Ties/Identify	SSM	B1.68
Heat Stabilized Nylon 6.6, Black (30)	Clamp Ties/Mount	SSC	B1.67

Part Number System for Sta-Strap® Cable Ties


SST	1	M	—	C	
Type	Size	Cross Section	Screw Hole Size	Package Size	Material/Color
SST = Locking Tie	Approx.	M = Miniature	(Clamp Ties Only)	L = 50	See Page B1.69
SSC = Clamp Tie	Maximum	I = Intermediate	-S6 = #6 (M3)	C = 100	
SSM = Flag Tie	Bundle	S = Standard	-S10 = #10 (M5)	D = 500	
	Dia. (In.)	H = Heavy	-S25 = 1/4 (M6)	M = 1000	
		HH = Heavy Head			



Sta-Strap® Cable Ties – Nylon 6.6

- For indoor use
- Used for normal bundling and through-panel applications
- Small head height allows more efficient use of space in compact areas

- Exclusive two-piece design offers the lowest threading force in the industry
- Average 14% lighter than one-piece cable ties
- Releasable prior to final tensioning for bundle modifications



	Length		Width		Thickness		Max. Bundle Dia.		Min. Loop Tensile Str.		Recommended Installation Tool	Std. Pkg. Qty.	Std. Ctn. Qty.
Part Number	In.	mm	In.	mm	In.	mm	In.	mm	Lbs.	N			
Miniature Cross Section													
SST1M-C	4.0	102	0.095	2.4	0.035	.9	.78	20	18	80	GTS-E, GS2B, PTS, PPTS, STS2	100	1000
SST1.5M-C	5.5	140	0.095	2.4	0.037	.9	1.25	32	18	80		100	1000
Intermediate Cross Section													
SST1.5I-C	5.3	137	0.135	3.4	0.037	.9	1.25	32	40	178	GTS-E, GS2B, PTS, PPTS, STS2	100	1000
SST2I-C	8.1	206	0.135	3.4	0.040	1.0	2.00	51	40	178		100	1000
SST3I-C	11.0	279	0.135	3.4	0.040	1.0	3.00	76	40	178		100	1000
SST4I-C	14.7	375	0.135	3.4	0.040	1.0	4.00	102	40	178		100	1000
Standard Cross Section													
SST1.5S-M	5.7	146	0.180	4.6	0.045	1.2	1.25	32	50	222	GTS-E, GS2B, GTH-E, GS4H, PTS, PTH, PPTS, STS2, STH2	1000	25000
SST2S-C	6.7	172	0.180	4.6	0.045	1.2	1.75	45	50	222		100	1000
SST3S-C	11.0	279	0.180	4.6	0.048	1.2	3.00	76	50	222		100	1000
SST4S-C	15.0	381	0.180	4.6	0.048	1.2	4.00	102	50	222		100	1000
Light-Heavy Cross Section													
SST2H-D	8.0	203	0.300	7.6	0.062	1.6	2.00	51	120	534	GTH-E, GS4H, GS4EH, PTH, STH2, ST3EH	500	5000
SST4H-L	14.8	376	0.300	7.6	0.067	1.7	4.00	102	120	534		50	500
SST8H-L	27.5	699	0.300	7.6	0.067	1.7	8.00	203	120	534		50	500

B1.
Cable
TiesB2.
Cable
AccessoriesB3.
Stainless
Steel Cable
Ties &
AccessoriesC1.
Wiring
DuctC2.
Abrasion
ProtectionC3.
Cable
ManagementD1.
TerminalsD2.
Power
ConnectorsD3.
Grounding
ConnectorsE1.
Labeling
SystemsE2.
LabelsE3.
Pre-Printed
&
Write-On
MarkersE4.
Permanent
IdentificationE5.
Industrial
Safety
SolutionsF.
Keystone
Cabling
SystemsG.
Part
Number
Index

Sta-Strap® Cable Ties

Material and Color Chart

Part Number	Color	Panduit Suffix
Nylon 6.6	Natural	✓
Weather Resistant Nylon 6.6	Black	0
Nylon 6.6	Red	2

✓Denotes Panduit® Natural Nylon 6.6 (no suffix).

Part Number	Color	Panduit Suffix
Nylon 6.6	Black	20
Heat Stabilized Nylon 6.6	Black	30

B1.
Cable
TiesB2.
Cable
AccessoriesB3.
Stainless
Steel Cable
Ties &
AccessoriesC1.
Wiring
DuctC2.
Abrasion
ProtectionC3.
Cable
ManagementD1.
TerminalsD2.
Power
ConnectorsD3.
Grounding
ConnectorsE1.
Labeling
SystemsE2.
LabelsE3.
Pre-Printed
&
Write-On
MarkersE4.
Permanent
IdentificationE5.
Industrial
Safety
SolutionsF.
Keystone
Cabling
SystemsG.
Part
Number
Index

Part Number Availability List

Standard Packaging			Bulk Packaging		
Part Number	Natural Nylon 6.6	Material/Color Suffix	Part Number	Natural Nylon 6.6	Material/Color Suffix
SSC2S-S6-C	✓		SSC2S-S6-M	✓	0
SSC2S-S10-C	✓		SSC2S-S10-M	✓	0,30
SSC4S-S10-C	✓		SSC4S-S10-M	✓	0
SSC4H-S25-L	✓		SSC4H-S25-D	✓	0
SSM2S-C	✓		SSM2S-D	✓	0
			SSM4S-D	✓	
SST1M-C	✓	0	SST1M-M	✓	0,20,30
SST1.5M-C	✓		SST1.5M-M	✓	0,20,30
SST1.5I-C	✓		SST1.5I-M	✓	0
SST2I-C	✓		SST2I-M	✓	0
SST3I-C	✓	0	SST3I-M	✓	0
SST4I-C	✓		SST4I-M	✓	0
			SST1.5S-M	✓	0
SST2S-C	✓	0	SST2S-M	✓	0,20,30
SST3S-C	✓	0	SST3S-M	✓	0,20,30
SST4S-C	✓	0	SST4S-M	✓	0,2,30
			SST2H-D	✓	0
			SST2HH-D		30
SST4H-L	✓	0	SST4H-D	✓	0,30
		0	SST4HH-D		30
SST8H-L	✓	0	SST8H-D	✓	0,30