

Panduct® Type FL Flexible Wiring Duct

- Material: Flexible Polypropylene
- UL 94 flammability rating of V-2
- UL Recognized continuous use temperature: 149°F (65°C)
- Factory applied adhesive tape provided for easy positioning**





Part Number	Duct Size (W x H)*		Length		Std. Pkg. Qty.
	mm	In.	mm	In.	
FL12X12LG-A	12.5 x 12.5	0.49 x 0.49	500	19.7	112
FL25X25LG-A	25.0 x 25.0	0.98 x 0.98	500	19.7	70
FL50X50LG-A	50.0 x 50.0	1.97 x 1.97	500	19.7	32

Available in LG (RAL 7040 Light Gray) color only. Unit of measure is pieces.

*"H" dimension includes duct and cover.

**Adhesive tape is not meant for permanent mounting of wiring duct. One mounting hole on each end will be exposed for permanent mounting with fasteners. For best results, wiring duct should be applied to clean, dry, grease-free surfaces. We recommend the surface be cleaned prior to wiring duct installation.



Panduct® Divider Wall

- Wiring duct divider wall can be mounted inside any type of Panduit PVC wiring duct to create multiple channels
- Meets UL508/508A insulation material requirement for barrier between conductors
- Simply install the divider wall base when mounting the duct and snap the divider wall onto the mounting base
- Divider Wall material: Lead-free PVC, UL 94 flammability rating of V-0
- All versions snap onto DB-C mounting base
- Mounting base material: Polycarbonate, UL 94 flammability rating of V-2
- Divider wall heights 2" and greater have a scoreline feature allowing sections to be removed leaving a smooth edge



Part Number	Used with Anchors	Std. Pkg. Qty.	Std. Ctn. Qty.
Panduct® Divider Wall Mounting Base			
DB-C	Panduit NR1 or #8, #10, M4 or M5 screw	100	1000



Part Number	For Nominal Duct Height		Length		Color	Std. Pkg. Qty.	Std. Ctn. Qty.
	In.	mm	Ft.	M			
Panduct® Solid Divider Wall							
D2H6	2.00	50	6	—	Light Gray	6	120
D3H6	3.00	75	6	—	Light Gray	6	120
D4H6	4.00	100	6	—	Light Gray	6	120
D2HWH6	2.00	50	6	—	White	6	120
D3HWH6	3.00	75	6	—	White	6	120
D4HWH6	4.00	100	6	—	White	6	120
D50H2	2.00	50	6	—	White	6	120
D75H2	3.00	75	6	—	White	6	120



Panduct® Slotted Divider Wall							
SD2H6	2.00	50	6	—	Light Gray	6	120
SD3H6	3.00	75	6	—	Light Gray	6	120
SD4H6	4.00	100	6	—	Light Gray	6	120
SD2HWH6	2.00	50	6	—	White	6	120
SD3HWH6	3.00	75	6	—	White	6	120
SD4HWH6	4.00	100	6	—	White	6	120

Note: Must be used with mounting base, DB-C (see page C1.30) which is sold separately. Install mounting bases to the duct channel, locate within 2" of each divider wall end and at least every 12" along the length.