


PRECISION GROUND SHAFTING — 1/32" To 1" Diameter

Nominal, Undersized and Oversized Diameters



Material: 303 Stainless Steel


Diameter Tolerance	
1/32 TO 1/2	+ .0000 - .0002
5/8 TO 1	+ .0000 - .0004

Fractional Dia. (Ref.)	D	L	Part No.
1/32	.0313	12	A8-1
	.0317		A8-23
1/16	.0622	12	A8-24
	.0626		A8-2
	.0630		A8-25
5/64	.0778	12	A8-20
	.0781		A8-22
	.0786		A8-26
3/32	.0934	12	A8-21
	.0938		A8-3
	.0942		A8-27
1/8	.1247	24	A8-6
	.1250		A8-5
	.1251	12	A8-4
	.1255	24	A8-28
5/32	.1559	24	A8-29
	.1562		A8-18
	.1567		A8-30
3/16	.1872	24	A8-9
	.1875		A8-7
	.1880		A8-31
7/32	.2184	24	A8-32
	.2187		A8-19
	.2192		A8-33
1/4	.2497	24	A8-11
	.2497	36	A8-34

Fractional Dia. (Ref.)	D	L	Part No.
1/4	.2500	24	A8-10
	.2500	36	A8-35
5/16	.3122	24	A8-13
	.3125		A8-12
3/8	.3747	16	A8-15
	.3747	36	A8-38
	.3750	16	A8-14
	.3750	36	A8-39
1/2	.4997	16	A8-17
	.4997	36	A8-41
	.5000	16	A8-16
	.5000	36	A8-42
5/8	.6247	36	A8-44
	.6250		A8-45
3/4	.7497	36	A8-47
	.7500		A8-48
1	.9997	36	A8-50
	1.0000		A8-51

For Pre-Cut and Chamfered Precision Ground Shafting, See A1 through A7 Series.
Other Lengths, Diameters and Modifications Available, Consult Factory.

ULTRA PRECISION SHAFTING — 1/8", 3/16" and 1/4" Diameter



Material: 303 Stainless Steel

Diameter	D	Straightness Tolerance
1/8	.12475	.0002
3/16	.18725	.00015
1/4	.24975	.0001

L	1/8 Dia. Part No.	3/16 Dia. Part No.	1/4 Dia. Part No.
1.00	A4-10	—	—
1.12	A4-11	—	—
1.25	—	A5-12	—
1.37	A4-13	—	—
1.50	—	A5-15	A6-15
1.75	A4-17	A5-17	—
1.88	A4-18	—	—
2.00	A4-20	A5-20	A6-20
2.50	—	—	A6-25
2.75	—	—	A6-27
3.00	—	A5-30	—
3.12	—	—	A6-31
3.25	A4-32	—	—
3.50	—	—	A6-35
4.00	—	—	A6-40
4.25	—	—	A6-42

Sold in increments of 5 pcs.
Other Lengths, Diameters and Modifications Available, Consult Factory.