

Riveting Systems

Rivet Presenter



Rotary bowl rivet feeding system

Used in conjunction with a POP® rivet tool the Rivet Presenter System offers single-handed, high-speed rivet feeding and setting. Automatic mandrel collection of up to 8500 mandrels can be achieved by adding the MCS5000 remote mandrel collector.

Each time the front of the rivet tool is inserted into the receptacle at the front of the Rivet Presenter a rivet is automatically and instantaneously loaded into the front of the tool. Rivets are stored in a rotary feeder bowl and continuously fed down a track into the receptacle ready for the next cycle.

Features & Benefits:

- Feeder bowl capacity up to 1,000 rivets
- Feeder bowl refilled in a few seconds
- Significant reductions in riveting cycle times possible
- Manual rivet feeding is eliminated enabling a white glove environment
- Single-handed operation leaves one hand free for other operations
- Enclosed feeder bowl and mandrel collection help keep working environment free from spilt rivets and mandrels

- For use with 3.2mm - 4.8mm rivets
- Height: 336mm, Length: 546mm, Width: 222mm, Weight: 10.4kg
- Air pressure: 5.8bar

DESCRIPTION	FOR RIVET DIAMETER	ARTICLE	RIVET CAPACITY
RP4E	3.2mm	14960	1,000 rivets
RP5E	4.0mm	14961	600 rivets
RP6E	4.8mm	14962	400 rivets