

## Speed Fastening® Systems

Reduce Assembly Costs with the most effective blind fastening technology.

Holding your world together®



## Speed fasteners

High precision, system-compatible function, ease of operation and quick processes are guaranteed because you can fasten continuously from magazine or bowl fed fasteners and place up to 60 fasteners per minute. For fast and reliable assembly processes.

Speed Fastening Systems can reduce assembly costs, shorten cycle times, increase productivity and reduce rework and other quality costs. Speed Fastening Systems are well suited for use in small, medium and large batch processes as well as continuous production lines.

## Installation

For smaller batches, we offer a choice of power tools and simple assembly workstations. For larger batches, multihead systems offer a cost effective solution. For continuous flow lines, we have the technology to develop fully automated assembly systems.

## Applications

Speed Fastening Systems can be used to assemble metal and plastics, composite material and electronic components. With an average cycle time of less than two seconds, these systems provide a fast installation from one side (blind).

## Mission

Together with our customers, we develop blind fastening systems that simplify your production process and improve the quality of your products. In every case, we not only see ourselves as a provider of fasteners, tools and machines but as a development and system partner with the objective of helping our customers improve their assembly performance.



# Table of Contents

---

Systems Range Overview	Speed Fastening® Systems	4	
	Range Overview	5	
	Specifying a Speed Fastening® System	6 - 7	
	Selection Guide	8 - 10	
The Range of Speed Fasteners	NeoSpeed®	11	
	Briv®	12	
	Chobert®	13	
	Double Flush Chobert®	14	
	Grovit®	15	
	Rivscrew®	16	
	Rivscrew® PL	17	
	Avtronic®	18	
	Avsert®	19	
	Avlug®	20	
	Customised Designs	21	
Installation Equipment	Installation Systems	22	
	Power Tools	23 - 24	
	Workstations	25 - 26	
	Assembly Workstations	27	
Data Sheets	NeoSpeed®	Fastener	28 - 33
		Equipment	34 - 35
	Briv®	Fastener	36 - 44
		Equipment	60 - 62
	Chobert®	Fastener	45 - 63
		Equipment	60 - 61, 63
	Double Flush Chobert®	Fastener	57
		Equipment	60 - 61, 63
	Grovit®	Fastener	58 - 59
		Equipment	60 - 61, 63
	Rivscrew®	Fastener	64 - 67
		Equipment	69 - 71
	Rivscrew® PL	Fastener	68
		Equipment	69 - 71
	Avtronic®	Fastener	72 - 73
		Equipment	74 - 75
	Avsert®	Fastener	76 - 77
		Equipment	78
	Avlug®	Fastener	79
		Equipment	80 - 81

# Speed Fastening<sup>®</sup> Systems

Speed Fastening is a unique assembly system designed for rapid and reliable fastening in medium and high volume applications. Originally designed for the aviation industry, Speed Fastening Systems are now used by many of the world's foremost manufacturing companies in sectors as diverse as household goods, lighting, electronic sub-assemblies, light metal fabrication and automotive. Speed fasteners are available in a wide range of materials, finishes, lengths and diameters and are ideal for fastening metals, plastics, composites and electronic components.

Speed fasteners are single piece fasteners which are either magazine fed or fed via a vibrating bowl to a wide choice of installation equipment. This ranges from the ultra-lightweight 753 power tool to fully automated, state of the art assembly systems.

## Benefits of assembly

### Increased manufacturing throughput

A Speed Fastening System can be fully optimised to give cycle times of less than two seconds. This rapid, blind sided process delivers a throughput up to four times greater than a traditional threaded or riveted solution.

### Reduced component handling

The fasteners are fed via a magazine or into a bowl feeder. This eliminates the need for individual component handling, saves time and reduces the potential for operator injury.

### No component spillage

Because the fasteners are captively held they will not be dropped onto the floor or into the application. This avoids wasted time and improves product quality while improving the work environment.

### No stem loss

Traditional breakstem rivets all too often suffer from stem loss once installed. This can lead to application rattle, electrical short circuits or worse. Speed fasteners have no stems.

### Improved joint quality

Speed installation technology provides a consistent, repeatable joint. What's more, unlike threaded fasteners, there is no requirement for torque control – no more problems of stripped holes or loose joints.

### Improved joint performance


Once installed speed fasteners give excellent clamp up, shear and tension performance. They are also virtually immune from vibration loosening.

### Process flexibility










Speed Fastening Systems can be used for low volume, off-line batch or jobbing shop work through to flow line processes. From hand held power tools to multi-headed modular workstations, we can design a Speed Fastening System to suit your assembly requirements. A wide variety of products in many industries are assembled with these systems including automotive, electronics, domestic appliance and general industrial.

## Time Analysis

Speed Fastening is the more efficient system after only 10 placed rivets.




# Range Overview

Brand		Material	Key features
NeoSpeed®		Aluminium Alloy Steel Stainless Steel A4	Wide grip range High joint clamp Hole filling Very high strength
Briv®		Aluminium Alloy Steel Stainless Steel A2 Brass	Bulbed tail form Large headform High joint clamp Good joint gap closure
Rivscrew®		Steel	Threaded fastener Removable with hex key and reusable Fastens into materials up to Vickers hardness 105 Hv5
Chobert®		Aluminium Alloy Steel Brass	Internal tapered bore Controlled clamp High shear Ideal for soft and brittle materials
Double Flush Chobert®		Steel	Flush surface on both sides of the joint Reduces excess space requirements within the chassis
Grovit®		Aluminium Alloy Steel	Designed for blind hole applications Annular grooves on body For use in wood, plastics, fibreglass and aluminium
Avtronic®		Brass Aluminium Alloy	Attaches DIN 41612 connectors and other components to PCBs Annular grooves on body
Avsert®		Brass	Threaded stand-off pillars for PCBs Internally threaded bore Many stand-off heights
Avlug®		Brass	Solderable terminal posts for PCBs Rolled/knurled shank


Assembly with standard tool



Fasteners fed via a vibrating bowl



Magazine fed fasteners



# Specifying a Speed Fastening® System

To optimise the performance of your Speed Fastening System, it is important to select the correct combination of fastener, nose equipment, mandrel and follower spring. It is also critical to ensure that the combination selected is suited for use with your choice of installation process. If you need any help in specifying the required components, do not hesitate to contact your local STANLEY Engineered Fastening representative. Further information on corrosion, safety and RoHS can be found on our website [www.StanleyEngineeredFastening.com](http://www.StanleyEngineeredFastening.com).

## Fastener Selection

### Standard Fasteners

#### Removability

Rivcrew® fasteners are ideal for applications requiring disassembly for repair or rework. They can simply be unscrewed using a standard hexagonal allen key.

#### Clamp

Briv® fasteners should be specified in applications requiring high clamp loads. NeoSpeed® fasteners combine high clamp throughout a wide grip range. Chobert® fasteners provide a lighter, controlled clamp making them ideal for softer or low strength materials.

#### Head Style

Fasteners are available with dome head. NeoSpeed®, Briv® and Chobert® are also available with countersunk head style. Other head diameters may also be available as specials – please contact your local STANLEY Engineered Fastening representative.

### Specialist Fasteners

#### Avtronic®

Designed for attaching DIN and other connectors, card ejectors and heatsinks to printed circuit boards.

#### Avsert®

Cost effective stand-off pillars for printed circuit boards.

#### Avlug®


Cost effective terminal posts for printed circuit boards.

### Fastener Material & Surface Finish

Speed fasteners are available in Stainless Steel, Steel, Aluminium and Brass. The choice of material should be made on the basis of performance (shear and tensile strength), suitability for use with the parent material and corrosion resistance. For performance data please see the relevant technical data sheets.



# Typical placing sequence



1. The mandrel with pre-loaded fastener is located in the hole.

2. Tool activation pulls the mandrel through the fastener, expanding it within the hole to provide high clamp and secure joints.


3. At the end of the installation cycle, the next fastener is automatically delivered to the nose of the tool, ready to repeat the assembly process.


Please visit our website [www.StanleyEngineeredFastening.com](http://www.StanleyEngineeredFastening.com) for fastener placing animations.

# The surface finishes for our speed fasteners are as follows:


Steel	Zinc plate and clear passivation Option: Epoxy paint Zinc-nickel (with clear or black passivation) Organic coatings
Aluminium Alloy	Natural Option: Anodising (clear or colour dyed) Epoxy paint
Stainless Steel	Passivated
Brass	Brightened Tin plated (for solderability)

Almost all our fastener families may be specified with alternative surface finishes to provide increased corrosion resistance or a specific colour to suit your special application.





This selection guide is designed to illustrate which fasteners may be the most suitable for your application. This guide does not include the full range of POP Avdel products; our Applications Engineers are available to advise as to the best solution for your specific application needs.






# Selection Guide

This table is designed as a guide to help you select the most suitable speed fastener for your particular application. Full technical and performance data for each speed fastener can also be found on our website or contact your local representative.


Product Range	Material						Finish						Head Style			Fastener Size (nom)										Series		Page							
	Aluminium 2.5 % Mg	Aluminium 3.5 % Mg	Aluminium 5 % Mg	Steel	Stainless Steel	Brass	Natural	Zinc plated	Polished/bright	Passivated	Tin plated	Nickel plated	Anodysed red	Dome	Low profile	Countersunk	1.6 mm (1/16")	2.4 mm (3/32")	2.5 mm	2.8 mm	3.0 mm	3.2 mm (1/8")	3.5 mm	4.0 mm (5/32")	4.5 mm	4.8 mm (3/16")	6.0 mm	6.4 mm (1/4")	M2.5	M3	Description	Data Sheet			
NeoSpeed®			•				•							•								•	•	•	•						57101	11	28		
				•				•						•								•	•	•	•						57121	11	30		
					•				•					•									•	•	•	•						57141	11	32	
				•				•								•						•									57221	11	33		
Briv®			•				•							•				•				•	•	•	•	•	•				1801	12	36		
			•				•									•		•				•	•	•	•	•	•				1802	12	38		
			•										•	•				•				•	•	•	•	•	•				1804	12	36		
				•				•						•				•				•	•	•	•	•	•				1821	12	39		
				•				•		•				•				•				•	•	•	•	•	•				1822	12	41		
						•			•					•				•				•	•	•	•	•					1831	12	42		
						•					•			•				•				•	•	•	•	•					1833	12	42		
	•				•				•					•				•				•	•	•	•	•					1841	12	44		
Chobert® Double Flush Chobert®							•							•							•	•	•	•	•		•				1861	12	36		
				•				•						•				•				•	•	•	•	•		•				1121	13	45	
				•				•								•		•				•	•	•	•	•		•				1122	13	47	
	•						•							•				•				•	•	•	•	•		•				1124	13	51	
	•						•							•				•				•	•	•	•	•		•				1125	13	49	
		•					•							•				•				•	•	•	•	•		•				1131	13	49	
			•				•							•				•				•	•	•	•	•		•				1132	13	51	
				•			•							•				•				•	•	•	•	•		•				1135	13	49	
							•							•				•				•	•	•	•	•		•				1136	13	51	
						•			•					•				•				•	•	•	•	•						1141	13	53	
						•				•				•				•				•	•	•	•	•						1142	13	53	
						•					•			•				•				•	•	•	•	•						1143	13	53	
						•						•		•				•				•	•	•	•	•						1144	13	53	
						•							•	•				•				•	•	•	•	•						1147	13	53	
	•						•						•	•				•				•	•	•	•	•						1148	13	53	
•						•							•	•						•	•	•	•	•							1162	13	55		
Grovit®				•			•		•					•				•				•	•	•	•	•						1164	13	56	
							•		•					•				•				•	•	•	•	•						1110	14	57	
	•						•		•					•				•				•	•	•	•	•						1101	15	58	
	•						•		•					•				•				•	•	•	•	•						1103	15	59	
RivscREW® PL RivscREW®							•							•				•				•	•	•	•							1722	16	64	
				•							•			•								•	•	•	•							1723	16	64	
				•										•								•	•	•	•							1733	16	66	
				•										•								•	•	•	•							1772	16	67	
				•										•								•	•	•	•	•						1742	17	68	
Avtronic®						•				•				•					•													1188	18	72	
		•					•							•					•													1189	18	73	
Avsert®						•				•																		•	•				1117	19	76
						•				•																		•	•				1118	19	77
Avlug®					•					•				•			•	•			•											1107	20	79	

## NeoSpeed® Nose Equipment

Ensembles de nez / Mundstücke / Equipaggiamento /  
Equipos de colocación



Nose equipment with addition of a twist cam to ease and speed up the nose jaw opening thus the pod reloading procedure.  
Ensembles de nez avec, en plus, une came facilitant et accélérant l'ouverture du nez de pose, et donc le rechargement en fixations.  
Zum leichteren Magazinieren haben diese Mundstücke durch einen Drehring zu öffnende Mundstückschnäbel.  
Equipaggiamento con l'aggiunta di una camma per facilitare e rendere più veloce l'apertura della testata e pertanto la procedura di ricarica dell'astuccio portarivetti.  
Boquillas que incorporan una leva para facilitar y hacer más rápida la apertura de la boquilla y el procedimiento de carga.






Applications with no or little access restrictions.  
Pour applications ne présentant que peu ou pas de contraintes d'accès.  
Für alle gut zugänglichen Nietpunkte.  
Adatta per applicazioni senza restrizioni di accesso o con restrizioni di accesso limitate.  
Apta para aquellas aplicaciones sin ninguna o pocas restricciones de acceso.

ø nom.	HeadStyle Forme de tête Kopfform Forma della testa Forma de cabeza	Nose Equipment Nez de pose Mundstück Testata Boquilla	Part No/ref	Dimensions Dimension / Abmessungen / Dimensioni / Dimensiones		
				B	D	E
3.2 (1/8")	Mushroom <sup>1)</sup>	Standard cam operated	07530-03200	10.41	29.97	5.08
	Countersunk <sup>2)</sup>	Standard tapered	07170-03104	10.41	30.23	5.08
4.0 (5/32")	Mushroom <sup>1)</sup>	Standard cam operated	07530-03300	12.90	33.02	6.10
4.8 (3/16")	Mushroom <sup>1)</sup>	Standard cam operated	07530-03400	14.22	29.97	8.38

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

<sup>1)</sup> Tête plate / Flachrundkopf / testa a fungo / cabeza alomada

<sup>2)</sup> Tête fraisée / Senkkopf / testa svasata / cabeza avellanada

Mandrel / Aiguille / Nietdorn / Spring / Ressort d'aiguille / Nietdornfeder /  
Mandrino / Mandril Molla / Muelle


Mandrel for stainless steel NeoSpeed

Ø nom.	Material Matériaux Material Materiale Material	Description Description Beschreibung Descrizione Descripción	Ø H nom.	P max.	Mandrel <sup>1)</sup> Part No/ref	Spring <sup>1)</sup> Part No/ref
3.2 (1/8")	Aluminium <sup>2)</sup> , Steel <sup>3)</sup>	Standard	2.30	3.05	07530-06014	07150-06814
	Stainless Steel <sup>4)</sup>	Standard	2.39	3.05	07530-06804	
4.0 (5/32")	Aluminium <sup>2)</sup> , Steel <sup>3)</sup>	Standard	2.67	3.45	07530-06015	07170-06875
	Stainless Steel <sup>4)</sup>	Standard	2.93	3.50	07530-06805	
4.8 (3/16")	Aluminium <sup>2)</sup> , Steel <sup>3)</sup>	Standard	3.53	3.99	07530-06016	07170-06876
	Stainless Steel <sup>4)</sup>	Standard	3.43	3.96	07530-06806	


all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

1) for use with paper magazine / pour utilisation avec chargeur papier / für Verarbeitung mit Papiermagazin / da usare con caricatori blister di carta / sólo para remaches en tiras de papel

2) Aluminium / Aluminium / Alluminio / Aluminio

3) Acier / Stahl / Acciaio / Acero

4) Inox / Edelstahl / Acciaio inox / Acero inoxidable




Applications with no or little access restrictions.

Pour applications ne présentant que peu ou pas de contraintes d'accès.

Für alle gut zugänglichen Nietpunkte.

Adatta per applicazioni senza restrizioni di accesso o con restrizioni di accesso limitate.

Apta para aquellas aplicaciones sin ninguna o pocas restricciones de acceso.




Allows access into very restrictive applications.

Permet d'accéder à des applications à accès très limité.

Für eng an den Bauteilseiten anliegende Nietpunkte.

Consente l'accesso ad applicazioni con serie restrizioni di accesso.




Permite el acceso en aplicaciones de acceso extremadamente limitado.



Allows more penetration into applications. Permet une pénétration supérieure dans les applications sans autres contraintes d'accès. Für tiefsitzende und eng an den Bauteilseiten anliegende Nietpunkte.

Consente una penetrazione maggiore nell'applicazione senza altre restrizioni di accesso.

Permite una mayor profundidad de acceso en aquellas aplicaciones sin restricción de acceso en anchura.




Nose equipment with addition of a twist cam to ease and speed up the nose jaw opening thus the pod reloading procedure.

Ensembles de nez avec, en plus, une came facilitant et accélérant l'ouverture du nez de pose, et donc le rechargement en fixations.

Zum leichteren Magazinieren haben diese Mundstücke durch einen Drehring zu öffnende Mundstückschnäbel.

Equipaggiamento con l'aggiunta di una camma per facilitare e rendere più veloce l'apertura della testata e pertanto la procedura di ricarica dell'astuccio portarivetti.

Boquillas que incorporan una leva para facilitar y hacer más rápida la apertura de la boquilla y el procedimiento de carga.



Type

- 1 - 7 Flat / Plat / Flach / Piatta / Plana
- 8 Tapered / Biseauté / Spitz / A punta / Conica
- 9 Universal / Universel / Für erhöhte Klammerkraft / Universale / concava
- 10 Recessed / En retrait / Spezial / Incassata / Apriete

Allows more penetration into applications.




Permet une pénétration supérieure dans les applications à accès limité.

Für tiefsitzende und eng an den Bauteilseiten anliegende Nietpunkte.

Consente una penetrazione maggiore nelle applicazioni con restrizioni di accesso.

Permite una mayor penetración en las aplicaciones con acceso limitado.

Mandrel / Aiguille / Nietdorn / Spring / Ressort d'aiguille / Nietdornfeder /  
Mandrino / Mandril Molla / Muelle



Mandrel for stainless steel Briv

Ø		Description Description Beschreibung Descrizione Descripción	Ø H	P	Standard Nose Equipment Nez de pose Standard Standard-Mundstück Testata Standard Boquilla Estándar		Long Nose Equipment Nez de pose Long Langes Mundstück Testata Lunga Boquilla Larga	
nom.				max.	Mandrel Part No/ref	Spring Part No/ref	Mandrel Part No/ref	Spring Part No/ref
2.4 (3/32") Aluminium, Brass	as rec.	Standard green	1.83	3.02	07150-06013	07150-06803 <sup>1)</sup>	N/A	N/A
	+ 0.10	1. oversize yellow	1.93	3.12	07150-06113			
	+0.20	2. oversize blue	2.01	3.20	07150-06213			
3.2 (1/8") Aluminium, Steel, Brass	as rec.	Standard green	2.34	3.05	07271-06414	07150-06814	07271-07414	07150-07814
	+ 0.13	1. oversize yellow	2.46	3.20	07271-06514		07271-07514	
	+ 0.25	2. oversize blue	2.59	3.38	07271-06614		07271-07614	
3.2 (1/8") Stainless Steel	as rec.	Standard green	2.53	3.07	07170-06804	07150-06814	07170-07804	07150-07814
	+ 0.13	1. oversize yellow	2.65	3.25	07170-06824		07170-07824	
4.0 (5/32") Aluminium, Steel, Brass	as rec.	Standard green	2.79	3.45	07150-06015	07170-06875	07150-07015	07170-07875
	+ 0.13	1. oversize yellow	2.92	3.61	07150-06115		07150-07115	
	+ 0.25	2. oversize blue	3.05	3.78	07150-06215		07150-07215	
4.0 (5/32") Stainless Steel	as rec.	Standard green	3.05	3.20	07170-06805	07170-06875	07170-07805	07170-07875
	+ 0.13	1. oversize yellow	3.15	3.35	07170-06825		07170-07825	
4.8 (3/16") Aluminium, Steel, Brass	as rec.	Standard green	3.58	3.99	07150-06016	07170-06876	07150-07016	07170-07876
	+ 0.13	1. oversize yellow	3.71	4.17	07150-06116		07150-07116	
	+ 0.25	2. oversize blue	3.84	4.32	07150-06216		07150-07216	
	+ 0.30	3. oversize red	3.85	4.39	07150-06316		07150-07316	
4.8 (3/16") Stainless Steel	as rec.	Standard green	3.81	3.81	07170-06806	07170-06876	07170-07806	07170-07876
	+ 0.13	1. oversize yellow	3.90	3.96	07170-06826		07170-07826	
6.0 Aluminium, Steel	as rec.	Standard green	4.54	4.18	07150-06018	07150-06846	07150-07018	07150-07846
	+ 0.13	1. oversize yellow	4.65	4.34	07150-06118		07150-07118	
	+ 0.25	2. oversize blue	4.79	4.49	07150-06218		07150-07218	

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

1) For use with standard flat nose piece. For tapered nose piece use spring 07170-06873 and for limited access nose piece use 07170-06903.

Pour utilisation avec nez de pose standard. Avec le nez de pose biseauté utilisez le ressort d'aiguille 07170-06873 et avec le nez de pose en retrait utilisez le 07170-06903.




Für Verwendung mit Standard Mundstück flach. Bei spitzem Mundstück verwenden Sie Feder 07170-06873 und bei abgesetztem Mundstück Feder 07170-06903.

Per uso con nasello standard a filo. Con nasello a punta usate molle 07170-06873 e con nasello incassata usate molle 07170-06903.

Para uso con boquilla estándar plana. Con boquilla cónica utilizar muelle 07170-06873 y con boquilla de acceso limitado utilizar 07170-06903.

English	Français	Deutsch	Italiano	Español
Aluminium	Aluminium	Aluminium	Alluminio	Aluminio
Brass	Laiton	Kupfer-Zink Leg.	Ottone	Latón
Steel	Acier	Stahl	Acciaio	Acero
Stainless Steel	Inox	Edelstahl	Acciaio inox	Acero inoxidable
Standard green	Standard verte	Standard grün	Standard verde	Estándar verde
1. oversize yellow	1. surdimensionnée jaune	1. Übermaß gelb	1. maggiorazione giallo	1. sobremedida amarillo
2. oversize blue	2. surdimensionnée bleue	2. Übermaß blau	2. maggiorazione blu	2. sobremedida azul
3. oversize red	3. surdimensionnée rouge	3. Übermaß rot	3. maggiorazione rosso	3. sobremedida rojo

Mandrel / Aiguille / Nietdorn / Spring / Ressort d'aiguille / Nietdornfeder /  
Mandrino / Mandril Molla / Muelle



Short Reach (S/R) mandrel

Ø nom.		Description Description Beschreibung Descrizione Descripción	Ø H	P max.	P S/R max.	Standard Nose Equipment Nez de pose Standard Standard-Mundstück Testata Standard Boquilla Estándar Mandrel <sup>1)</sup> Part No/ref	Spring Part No/ref	Long Nose Equipment Nez de pose Long Langes Mundstück Testata Lunga Boquilla Larga Mandrel <sup>3)</sup> Part No/ref	Spring Part No/ref
2.4 (3/32") Brass, Aluminium	as rec. + 0.04 + 0.09	Standard green 1. oversize yellow 2. oversize blue	1.84 1.88 1.93	4.22 4.42 4.70	1.80 1.98 N/A	07150-06003 07150-06303 <sup>1)</sup> 07150-06103	07150-06803 <sup>2)</sup>	07150-07003 S/R only =07150-09103 07150-07103	07150-07803
3.2 (1/8") Aluminium Steel, Brass Chobert® / Grovit®	as rec. + 0.10 + 0.25 + 0.35	Standard green 1. oversize yellow 2. oversize blue 3. oversize red	2.24 2.34 2.49 2.59	5.49 6.02 6.81 7.32	2.29 2.49 2.79 3.00	07150-06004 07150-06104 07150-06204 07150-06304	07150-06804	07150-07004 07150-07104 07150-07204 07150-07304	07150-07804
3.2 (1/8") Double Flush Chobert®	as rec. + 0.10 + 0.25	Standard green 1. oversize yellow 2. oversize blue	2.24 2.34 2.49	N/A N/A N/A	2.29 2.49 2.79	07150-08004 07150-08104 07150-08204	07271-06630	N/A	N/A
4.0 (5/32") Aluminium, Steel, Brass	as rec. + 0.20 + 0.38 + 0.63	Standard green 1. oversize yellow 2. oversize blue 3. oversize red	2.72 2.92 3.10 3.35	6.20 7.21 8.13 9.45	2.54 2.95 3.30 3.81	07150-06005 07150-06105 07150-06205 07150-06305	07170-06875 07150-06805	07150-07005 07150-07105 07150-07205 07150-07305	07170-07875 07150-07805
4.8 (3/16") Aluminium, Steel, Brass	as rec. + 0.35 + 0.60	Standard green 1. oversize yellow 2. oversize blue	3.35 3.71 3.96	6.27 8.13 9.45	2.59 3.30 3.81	07150-06006 07150-06106 07150-06206	07170-06876 07150-06806	07150-07006 07150-07106 07150-07206	07170-07876 07150-07806
6.4 (1/4") Alum., Steel	as rec. + 0.30	Standard green 1. oversize yellow	4.67 4.98	6.81 8.38	2.79 3.40	07150-06008 07150-06108	07150-06808	07150-07008 07150-07108	07150-07808

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

- 1) For S/R mandrel substitute 6 with 8 (07150-06xxx => 07150-08xxx), exception: 07150-06303 becomes 07150-08103.  
Pour aiguille S/R remplacer 6 par 8 (07150-06xxx => 07150-08xxx), exception: 07150-06303 change à 07150-08103.  
Für S/R Nietdorn ersetzen Sie 6 durch 8 (07150-06xxx => 07150-08xxx), Ausnahme: 07150-06303 wird zu 07150-08103.  
Per mandrino S/R sostituire 6 con 8 (07150-06xxx => 07150-08xxx), eccezione: 07150-06303 cambia 07150-08103.  
Con mandril cono corto S/R cambiar 6 por 8 (07150-06xxx => 07150-08xxx), excepción: 07150-06303 cambia a 07150-08103.
- 2) For use with standard flat nose piece. Tapered nose piece uses spring 07170-06873 and limited access nose piece uses 07170-06903.  
Pour utilisation avec nez de pose standard. Avec le nez de pose biseauté utilisez le ressort d'aiguille 07170-06873 et avec le nez de pose en retrait utilisez le 07170-06903.  
Für Verwendung mit Standard Mundstück flach. Bei spitzem Mundstück verwenden Sie Feder 07170-06873, bei abgesetztem Mundstück Feder 07170-06903.  
Per uso con nasello standard a filo. Con nasello a punta usate molle 07170-06873 e con nasello incassata usate molle 07170-06903.  
Para uso con boquilla estándar plana. Con boquilla cónica utilizar muelle 07170-06873 y con boquilla de acceso limitado utilizar 07170-06903.
- 3) For S/R mandrel substitute 7 with 9 (07150-07xxx => 07150-09xxx)  
Pour aiguille S/R remplacer 7 par 9 (07150-07xxx => 07150-09xxx)  
Für S/R Nietdorn ersetzen Sie 7 durch 9 (07150-07xxx => 07150-09xxx)  
Per mandrino S/R sostituire 7 con 9 (07150-07xxx => 07150-09xxx)  
Con mandril cono corto S/R cambiar 7 por 9 (07150-07xxx => 07150-09xxx)

English	Français	Deutsch	Italiano	Español
Aluminium	Aluminium	Aluminium	Alluminio	Aluminio
Brass	Laiton	Kupfer-Zink Leg.	Ottone	Latón
Steel	Acier	Stahl	Acciaio	Acero
Stainless Steel	Inox	Edelstahl	Acciaio inox	Acero inoxidable
Standard green	Standard verte	Standard grün	Standard verde	Estándar verde
1. oversize yellow	1. surdimensionnée jaune	1. Übermaß gelb	1. maggiorazione giallo	1. sobremedida amarillo
2. oversize blue	2. surdimensionnée bleue	2. Übermaß blau	2. maggiorazione blu	2. sobremedida azul
3. oversize red	3. surdimensionnée rouge	3. Übermaß rot	3. maggiorazione rosso	3. sobremedida rojo