


# Avibulb® BN01

For installation information please refer to the tooling overview and manuals on our website [www.avdel-global.com](http://www.avdel-global.com).  
 Pour les conditions de pose, merci de vous référer à la description de l'outil et aux manuels disponibles sur notre site Web.  
 Angaben zur Verarbeitung entnehmen Sie bitte der Geräteübersicht und den Betriebsanleitungen auf unserer Website.  
 Per informazioni sull'installazione preghiamo consultare i manuali e la panoramica degli attrezzi sul nostro sito web.  
 Para ver información sobre máquinas de colocación, consulte nuestra página web, apartados visión general de máquinas y manuales.



| English                     | Français                      | Deutsch                    | Italiano                                    | Español                           |
|-----------------------------|-------------------------------|----------------------------|---------------------------------------------|-----------------------------------|
| Dome head                   | Tête plate                    | Flachrundkopf              | Testa tonda                                 | Cabeza alomada                    |
| Body: Low carbon steel*     | Corps: Acier bas carbone*     | Hülse: Stahl*              | Corpo: Acciaio a basso tenore di carbonio*  | Cuerpo: Acero bajo en carbono*    |
| Zinc plated                 | Revêtement zingué             | Verzinkt                   | Zincato                                     | Zincado                           |
| Clear trivalent passivated  | Passivation claire trivalente | Klar chromatiert, Cr6-frei | Passivazione chiara trivalente              | Pasivado claro trivalente         |
| Stem: Medium carbon steel** | Tige: Acier au carbone**      | Dorn: Stahl**              | Gambo: Acciaio a medio tenore di carbonio** | Vástago: Acero medio en carbono** |
| Zinc plated                 | Revêtement zingué             | Verzinkt                   | Zincato                                     | Zincado                           |
| Clear trivalent passivated  | Passivation claire trivalente | Klar chromatiert, Cr6-frei | Passivazione chiara trivalente              | Pasivado claro trivalente         |

\*: BS3111 Type 0, SAE 1008, DIN 1654, QSt 34-3 / BS3111 Type 0, SAE 1015 DIN 1711, RSt 38-2, Werkstoff 1.0401  
 \*\*: BS3111 Type 1, SAE 1030/1037/1040/1045, Werkstoff 1.1178/1.1176/1.1186/1.1191



| Ø                 |      |      |      |      | M    | B    | D    | E    |                       |                     | Part No/ref |
|-------------------|------|------|------|------|------|------|------|------|-----------------------|---------------------|-------------|
| nom.              | min. | max. | min. | max. | max. | max. | max. | max. | lb f <sup>(1)2)</sup> | lb f <sup>(1)</sup> |             |
| 1/8"<br>(3.2 mm)  | .039 | .118 | .130 | .134 | .358 | .268 | .055 | .080 | 270                   | 292                 | OBN01-00408 |
|                   | .118 | .197 |      |      | .461 |      |      |      | 393                   |                     | OBN01-00411 |
|                   | .197 | .276 |      |      | .551 |      |      |      | 562                   |                     | OBN01-00414 |
| 5/32"<br>(4.0 mm) | .039 | .118 | .161 | .169 | .409 | .315 | .059 | .103 | 539                   | 629                 | OBN01-00509 |
|                   | .118 | .197 |      |      | .508 |      |      |      | 787                   |                     | OBN01-00512 |
|                   | .197 | .276 |      |      | .618 |      |      |      | 921                   |                     | OBN01-00516 |
|                   | .275 | .354 |      |      | .713 |      |      |      | 740                   | 562                 | OBN01-00519 |
| 3/16"<br>(4.8 mm) | .059 | .138 | .193 | .201 | .476 | .378 | .059 | .126 | 809                   | 854                 | OBN01-00611 |
|                   | .138 | .236 |      |      | .579 |      |      |      | 944                   |                     | OBN01-00614 |
|                   | .236 | .335 |      |      | .693 |      |      |      | 1258                  |                     | OBN01-00618 |
| 6.0 mm            | .059 | .157 | .240 | .248 | .551 | .484 | .083 | .158 | 944                   | 1213                | OBN01-06010 |
|                   | .118 | .236 |      |      | .669 |      |      |      | 1213                  |                     | OBN01-06013 |
|                   | .236 | .354 |      |      | .787 |      |      |      | 1910                  |                     | OBN01-06016 |
|                   | .335 | .472 |      |      | .906 |      |      |      | 1910                  |                     | OBN01-06019 |

all dimensions in inches / en pouces / alle Maße in Zoll / in pollici / en pulgadas

1) typical values / valeurs moyennes / typische Werte / Valori tipici / resistencias máximas recomendadas

2) through stem / avec tige / bei tragendem Restdorn / attraverso il gambo / con el vástago en la zona de cortadura



An Acument™ Global Technologies Company

[www.avdel-global.com](http://www.avdel-global.com)

© 2007 Acument Intellectual Properties, LLC

Avibulb® is a trademark of Avdel UK Limited

03.2010

Data shown is subject to change without prior notice as a result of continuous product development and improvement policy.  
 Your local Avdel representative is at your disposal should you need to confirm latest information.