



Q Rivet BSPQ / BSLQ /BSCQ




English	Français	Deutsch	Italiano	Español
Body: Aluminium alloy* (5 % Mg) Natural	Corps: Alliage d'aluminium* (5% Mg) Brut	Hülse: Aluminium* (5 % Mg) Blank	Corpo: Lega di alluminio* (5% Mg) Nessuna finitura	Cuerpo: Aluminio* (5% Mg) Natural
Stem: Steel** Zinc plated	Tige: Acier** Revêtement zingué	Dorn: Stahl** verzinkt	Gambo: Acciaio** Zincati	Vástago: Acero** Zincado
*: BS 1473 5056 DIN 1725 AlMg5 Werkstoff 3.3555				
**: BS3111 Type 1 SAE 1038 DIN 1654 Cq35				



Q Rivet BSPQ
Protruding head / Tête bombée /
Flachrundkopf / Testa tonda /
Cabeza alomada



Q Rivet BSLQ
Large flange / Tête large /
Flachrundkopf, extragroß /
Testa larga / Cabeza ancha



Q Rivet BSCQ
Countersunk / Tête fraisée
Senkkopf / Testa svasata
Cabeza avellanada

Ø						M	Ø E	BSPQ Protruding head			BSLQ Large flange			BSCQ Countersunk		
	nom.	min.	mid. ¹⁾	max.	min.	max.	ref.	Ø B	D	Part No. /ref BSPQ-	Ø B	D	Part No. /ref BSLQ-	Ø B	D	Part No. /ref BSCQ-
1/8" (3.2 mm)			.062			.212				-04-01						
		.063	.093	.125		.275				-04-02			-04-02			
		.094	.140	.187		.337				-04-03						-04-03
		.126	.187	.250		.400				-04-04			-04-04			-04-04
		.188	.250	.312		.462		.250 ±.012	.042	-04-05			-04-05			-04-05
		.251	.312	.375		.535				-04-06			-04-06			-04-06
		.313	.375	.437		.602				-04-07						-04-07
		.376	.437	.500		.670				-04-08			-04-08			-04-08
					.129	.133	.075				.375 ±.015	.065		.226	.032	
5/32" (4.0 mm)		.062	.093	.125		.300				-05-02						
		.094	.140	.187		.362				-05-03						
		.126	.187	.250		.425		.312 ±.016	.050	-05-04			-05-04			-05-04
		.251	.312	.375		.550				-05-06			-05-06			-05-06
		.376	.437	.500		.695				-05-08			-05-08			-05-08
3/16" (4.8 mm)		.062	.093	.125		.325				-06-02						
		.094	.140	.187		.387				-06-03						
		.126	.187	.250		.450				-06-04						-06-04
		.188	.250	.312		.512				-06-05						-06-05
		.251	.312	.375		.575		.375 ±.019	.060	-06-06			-06-06			-06-06
		.376	.437	.500		.700				-06-08			-06-08			-06-08
		.501	.562	.625		.850				-06-10			-06-10			-06-10
		.626	.687	.750		.980				-06-12			-06-12			-06-12
		.751	.812	.875		1.110				-06-14			-06-14			-06-14
					.192	.196	.114				.625 ±.025	.092		.344	.050	

all dimensions in inches / en pouces / alle Maße in Zoll / in pollici / en pulgadas

1) Mandrels break flush with rivet head at mid. grip (except -04-01s, which break at .062) / La tige rompt affleurante à la tête du rivet en milieu de plage de serrage (sauf pour -04-01s qui rompt à .062) / Bei mittlerem Klemmbereich (mid.) reißt der Dorn bündig mit dem Nietkopf ab (außer -04-01, der bei .062 abreißt) / Q Rivet rottura del chiodo a livello della testa del rivetto per grip medio (eccetto -04-01s rottura a .062) / El punto de rotura del Q Rivet es a ras con la cabeza del remache en su grip intermedio (excepto el -04-01s. que rompe a .062)



An Acument™ Global Technologies Company

www.avdel-global.com

© 2007 Acument Intellectual Properties, LLC

10.2007, page 1/2

Data shown is subject to change without prior notice as a result of continuous product development and improvement policy.
Your local Avdel representative is at your disposal should you need to confirm latest information.

Q Rivet BSPQ / BSLQ /BSCQ

Ø nom.						M max.	Ø E ref.	BSPQ Protruding head			BSLQ Large flange			BSCQ Countersunk		
	min.	mid. ¹⁾	max.	min.	max.			Ø B	D max.	Part No. /ref BSPQ-	Ø B	D max.	Part No. /ref BSLQ-	Ø B ±.007	D ref.	Part No. /ref BSCQ-
1/4" (6.4 mm)	.062	.093	.125	.257	.261	.375	.151	.500 ±.025	.078	-08-02	.750 ±.025	.107	-08-02	.468	.071	-08-02
	.126	.187	.250			.500				-08-04			-08-04			-08-04
	.251	.312	.375			.625				-08-06			-08-06			-08-06
	.376	.437	.500			.750				-08-08			-08-08			-08-08
	.501	.562	.625			.900				-08-10			-08-10			-08-10
	.626	.687	.750			1.030				-08-12			-08-12			-08-12
	.751	.812	.875			1.160				-08-14			-08-14			-08-14
	.876	.937	1.000			1.290				-08-16			-08-16			-08-16
	1.001	1.062	1.125			1.420				-08-18						
	1.126	1.187	1.250			1.550				-08-20						

all dimensions in inches / en pouces / alle Maße in Zoll / in pollici / en pulgadas

1) Mandrels break flush with rivet head at mid. grip (except -04-01s, which break at .062) / La tige rompt affleurante à la tête du rivet en milieu de plage de serrage (sauf pour -04-01s qui rompt à .062) / Bei mittlerem Klemmbereich (mid.) reißt der Dorn bündig mit dem Nietkopf ab (außer -04-01, der bei .062 abreißt) / Q Rivet rottura del chiodo a livello della testa del rivetto per grip medio (eccetto -04-01s rottura a .062) / El punto de rotura del Q Rivet es a ras con la cabeza del remache en su grip intermedio (excepto el -04-01s. que rompe a .062)

Ø nom.	 lbf ²⁾	 lbf ²⁾
1/8" (3.2 mm)	350	325
5/32" (4.0 mm)	525	450
3/16" (4.8 mm)	750	650
1/4" (6.4 mm)	1250	1050

2) typical values / valeurs moyennes / typische Werte / Valori tipici / resistencias máximas recomendadas



An Acument™ Global Technologies Company

www.avdel-global.com

© 2007 Acument Intellectual Properties, LLC

10.2007, page 2/2

Data shown is subject to change without prior notice as a result of continuous product development and improvement policy.
Your local Avdel representative is at your disposal should you need to confirm latest information.