





Miniature Through/Ground Conductor and Ex Terminal Blocks for DIN-35 Rail



























2.5 mm², 264 Series

0.08 ... 2.5 mm ² 800 V/8 kV/3 ① I _N 24 A	28 ... 12 AWG* 300 V, 20 A ② 600 V, 20 A ③	0.08 ... 2.5 mm ² 800 V/8 kV/3 ① I _N 24 A	28 ... 12 AWG* 300 V, 20 A ② 600 V, 20 A ③
Terminal block width 6 mm / 0.236 inch  8 ... 9 mm / 0.31 ... 0.35 inch		Terminal block width 10 mm / 0.394 inch  8 ... 9 mm / 0.31 ... 0.35 inch	



* 12 AWG: THHN, THWN

- ① 800 V = rated voltage
8 kV = rated surge voltage
3 = pollution degree
(see Section 14)
- ② Suitable for Ex i applications
- ③ Suitable for Ex e II applications
0.5 ... 2.5 mm² / 20 ... 12 AWG*
690 V, 23 A
(see Section 14)
- ④ See application notes for:
Alternate comb-style jumper bar, page 332
Test plug module, page 456

Item No.	Pack. Unit	Item No.	Pack. Unit	264 Series Accessories
2-conductor miniature through terminal block, for DIN-35 rail		4-conductor miniature through terminal block, for DIN-35 rail		Mini-WSB/Mini-WSB Inline (see Section 13)
 gray 264-711	100	 gray 264-731	100	End and intermediate plate, 4 mm thick
 blue 264-714 ②	100	 blue 264-734 ②	100	 orange 264-369 25
 orange 264-716	100	 orange 264-736	100	 gray 264-368 25
 light gray ⑤ 264-125 ③	100	 light gray ⑤ 264-225 ③	100	 light gray 264-370 25
Item-Specific Accessories		Item-Specific Accessories		Separator for Ex e/Ex i applications, orange, 4 mm thick
Alternate comb-style jumper bar, insulated, I _N = I _N terminal block ④		Alternate comb-style jumper bar, insulated, I _N = I _N terminal block ④		 66 mm 264-367 25
 2-way 281-492	100 (4x25)	 2-way 280-492	200 (8x25)	Comb-style jumper bar, insulated, I _N 16 A, gray, reduces maximum conductor size to 1.5 mm ² / 16 AWG
Test plug module, snaps together, 6 mm wide ④		Test plug module, snaps together, 10 mm wide ④		 2-way 264-402 200 (8x25)
 gray 249-136	100 (4x25)	 gray 249-139	100 (4x25)	Operating tool, of insulating material
				 2-way 280-432 1
				Test plug, with 500 mm cable, 2 mm Ø, max. 42 V
				 red 210-136 50
				Test plug, with 500 mm cable, 2.3 mm Ø, max. 42 V
				 yellow 210-137 50
				Mini-WSB Quick marking system, white, 10 strips with 10 markers per card, 5 mm wide markers
				 plain 248-501 5
				Screwless end stop, for DIN-35 rail, 6 mm wide
				 gray 249-116 100 (4x25)
				Screwless end stop, for DIN-35 rail, 10 mm wide
				 gray 249-117 50 (2x25)
				Steel carrier rail, per EN 60715, 35 x 7.5 mm, 1 mm, 2 m long
				 slotted 210-112 10 (10x1)
				Steel carrier rail, per EN 60715, 35 x 7.5 mm, 1 mm, 2 m long
				 unslotted 210-113 10
				Aluminum carrier rail, similar to EN 60715, 35 x 8.2 mm, 1.6 mm, 2 m long
				 unslotted 210-196 10

