


WASHERS

STYLE	SHAFT SIZE	MATERIAL
BELLEVILLE	3/32 TO 3/4	302 STAINLESS STEEL *1095 CARBON STEEL




STOCK NO.	O.D. ±.010	I.D. +.001 -.000	T ±10%	HF (Ref.)	HC	FORCE TO COMPRESS TO HC ± 15%
ST-1	.187	.093	.010	.015	.012	15 LBS
ST-2	.250	.125	.013	.020	.017	26 LBS
ST-3	.312	.156	.016	.025	.021	41 LBS
ST-4	.375	.190	.020	.030	.025	60 LBS
ST-5	.500	.255	.025	.038	.031	95 LBS
ST-6	.625	.317	.032	.048	.040	145 LBS
ST-7	.750	.380	.040	.059	.049	235 LBS
ST-8	1.000	.505	.050	.075	.062	340 LBS
ST-9	1.250	.630	.062	.092	.077	475 LBS
ST-10*	1.500	.750	.072	.107	.089	660 LBS



Sold in packages of 10.

STYLE	SHAFT SIZE	MATERIAL
CURVED	3/32 TO 3/4	302 STAINLESS STEEL *1095 CARBON STEEL



STOCK NO.	SCREW OR ROD SIZE	HOLE SIZE	O.D. ±.010	I.D. † +.010 -.000	HF (Ref.)	T ±10%	HC	FORCE TO COMPRESS TO HC ± 15%
SU-1	#5	1/4	.245	.135	.034	.006	.020	2 LBS
SU-2	#6	9/32	.270	.148	.035	.007	.022	2 LBS
SU-3	#8	11/32	.322	.174	.042	.007	.025	3 LBS
SU-4	#10	3/8	.370	.200	.047	.009	.028	4 LBS
SU-5	#12	7/16	.423	.231	.053	.010	.032	5 LBS
SU-6	1/4	1/2	.490	.265	.063	.011	.034	7 LBS
SU-7*	9/32	9/16	.551	.296	.070	.012	.038	8 LBS
SU-8	5/16	5/8	.612	.327	.077	.013	.042	9 LBS
SU-9*	11/32	11/16	.672	.363	.081	.015	.047	11 LBS
SU-10	3/8	3/4	.735	.395	.086	.016	.050	12 LBS
SU-11*	7/16	7/8	.857	.462	.100	.018	.057	15 LBS
SU-12	1/2	1	.980	.525	.110	.021	.063	20 LBS

† I.D. Based in long axis providing free fit on normal screw.

Sold in packages of 10.

