


STAINLESS GROUND SHAFTS

| DIAMETER | MATERIAL |
|-------------|----------------------------|
| 3MM TO 30MM | STAINLESS STEEL DIN 1.4305 |



| STOCK NO. | FRACT. DIA. REF. | ACTUAL DIA. | DIAMETER TOL. | L |
|-----------|------------------|-------------|------------------|-----|
| S1-103 | 3 | 2.992 | +0.000 -0.005 | 600 |
| S1-131 | | 3.000 | | 600 |
| S1-132 | | 3.003 | | 300 |
| S1-133 | | 3.003 | | 600 |
| S1-104 | 4 | 3.992 | | 600 |
| S1-134 | | 3.999 | | 600 |
| S1-105 | 5 | 4.991 | | 900 |
| S1-135 | | 5.000 | | 600 |
| S1-106 | 6 | 5.992 | | 900 |
| S1-136 | | 6.000 | | 900 |
| S1-137 | 7 | 6.992 | | 900 |
| S1-138 | | 6.992 | | 600 |
| S1-139 | | 7.000 | | 900 |
| S1-140 | | 7.000 | | 600 |
| S1-108 | 8 | 7.993 | | 900 |
| S1-141 | | 8.000 | | 600 |
| S1-109 | 9 | 8.992 | | 900 |
| S1-110 | 10 | 9.992 | +0.000 -0.005 | 900 |
| S1-142 | | 10.000 | | 400 |
| S1-143 | | 10.000 | | 900 |
| S1-144 | 12 | 11.991 | +0.000 -0.005 | 400 |
| S1-112 | | 11.991 | | 900 |
| S1-145 | | 12.000 | | 400 |
| S1-146 | | 12.000 | | 900 |
| S1-149 | 13 | 12.993 | +0.000 -0.008 | 400 |
| S1-113 | | 12.993 | | 900 |
| S1-114 | 14 | 13.993 | +0.000 -0.008 | 900 |
| S1-116 | 16 | 15.974 | | 900 |
| S1-147 | | 16.000 | | 900 |
| S1-120 | 20 | 19.992 | | 900 |
| S1-125 | 25 | 24.993 | | 900 |
| S1-148 | | 25.000 | | 900 |
| S1-130 | 30 | 29.992 | | 900 |

* Straightness: 10 mm diameter and above .0101 mm/mm. 6mm diameter and below on best efforts basis.