













Nominal Rivet Diameter	(L) Nominal Rivet Body Length	(F) Nominal Blind Side Protrusion		Rivet Part Number							
						(D) Body Diameter	(H) Flange Thickness	(E) Flange Diameter	(W) Nominal Mandrel Diameter		
In. (mm)	In. (mm)	In. (mm)	In. (mm)		In. (mm)	In. (mm)	In. (mm)	In. (mm)		Lbs. (N)	Lbs. (N)
C1006-C1010 Steel Body/Steel Mandrel – Large Flange – Finish: Zinc/Protective Coating											
3/16 (4.8)	.300 (7.6)	.460 (11.7)	.063-.125 (1.6-3.2)	SD 62 BS LF	.192-.196 (4.88-4.98)	.183-.191 (4.65-4.85)	.067-.083 (1.70-2.11)	.600-.650 (15.24-16.51)	.114 (2.90)	590 (2624)	815 (3625)
	.425 (10.8)	.585 (14.9)	.126-.250 (3.2-6.4)	SD 64 BS LF							
	.550 (14.0)	.710 (18.0)	.251-.375 (6.4-9.5)	SD 66 BS LF							
	.675 (17.2)	.835 (21.2)	.376-.500 (9.5-12.7)	SD 68 BS LF							
	.800 (20.3)	.960 (24.4)	.501-.625 (12.8-15.9)	SD 610 BS LF							
	.925 (23.5)	1.085 (27.6)	.626-.750 (15.9-19.1)	SD 612 BS LF							
1.4 (6.4)	.600 (15.2)	.835 (21.2)	.251-.375 (6.4-9.5)	SD 86 BS LF	.257-.261 (6.53-6.63)	.249-.255 (6.32-6.48)	.098-.107 (2.49-2.72)	.720-.780 (18.29-19.81)	.151 (3.84)	1245 (5538)	1505 (6694)
	.850 (21.6)	1.085 (27.6)	.501-.625 (12.7-15.8)	SD 810 BS LF							
	1.100 (27.9)	1.335 (33.9)	.751-.875 (19.1-22.2)	SD 814 BS LF							
Nominal Rivet Diameter	(L) Nominal Rivet Body Length	(F) Nominal Blind Side Protrusion		Rivet Part Number							
						(D) Body Diameter	(H) Flange Thickness	(E) Flange Diameter	(W) Nominal Mandrel Diameter		
C1006-C1010 Steel Body/Steel Mandrel – 120° Countersunk – Finish: Zinc/Protective Coating											
3/32 (2.4)	.225 (5.8)	.325 (8.3)	.063-.125 (1.6-3.2)	SK 32 BS	.097-.100 (2.46-2.54)	.092-.096 (2.34-2.44)	.039 Max (0.99)	.161-.187 (4.09-4.75)	.057 (1.45)	150 (667)	205 (912)
1/8 (3.2)	.250 (6.4)	.370 (9.4)	.063-.125 (1.6-3.2)	SK 42 BS	.129-.133 (3.28-3.38)	.122-.128 (3.10-3.25)	.051 Max (1.30)	.207-.233 (5.26-5.92)	.076 (1.93)	295 (1312)	425 (1891)
	.313 (8.0)	.433 (11.0)	.126-.187 (3.2-4.8)	SK 43 BS							
	.375 (9.5)	.495 (12.6)	.188-.250 (4.8-6.4)	SK 44 BS							
	.500 (12.7)	.620 (15.7)	.313-.375 (7.9-9.5)	SK 46 BS							
5/32 (4.0)	.650 (16.5)	.790 (20.1)	.376-.500 (9.6-12.7)	SK 58 BS	.160-.164 (4.06-4.17)	.153-.159 (3.89-4.04)	.063 Max (1.60)	.266-.296 (6.75-7.52)	.095 (2.41)	410 (1824)	570 (2535)
3/16 (4.8)	.425 (10.8)	.585 (14.9)	.126-.250 (3.2-6.4)	SK 64 BS	.192-.196 (4.88-4.98)	.183-.191 (4.65-4.85)	.071 Max (1.80)	.333-.363 (8.46-9.22)	.114 (2.90)	590 (2624)	815 (3625)