






# TOPJOB® S









































## Through/Ground Conductor/Shield and Ex Terminal Blocks

### 2.5 (4) mm<sup>2</sup>, 2002 Series

1





















0.25 ... 2.5 (4) mm <sup>2</sup> ① 800 V/8 kV/3 ② I <sub>N</sub> 24 A (32 A)	22 ... 12 AWG 600 V, 20 A ③ 600 V, 20 A ④	0.25 ... 2.5 (4) mm <sup>2</sup> ① 800 V/8 kV/3 ② I <sub>N</sub> 24 A (32 A)	22 ... 12 AWG 600 V, 20 A ③ 600 V, 20 A ④	0.25 ... 2.5 (4) mm <sup>2</sup> ① 800 V/8 kV/3 ② I <sub>N</sub> 24 A (32 A)	22 ... 12 AWG 600 V, 20 A ③ 600 V, 20 A ④
Terminal block width 5.2 mm / 0.205 inch  10 ... 12 mm / 0.39 ... 0.47 inch		Terminal block width 5.2 mm / 0.205 inch  10 ... 12 mm / 0.39 ... 0.47 inch		Terminal block width 5.2 mm / 0.205 inch  10 ... 12 mm / 0.39 ... 0.47 inch	



Item No.	Pack. Unit	Item No.	Pack. Unit	Item No.	Pack. Unit
2-conductor through terminal block		3-conductor through terminal block		4-conductor through terminal block	
 gray ④ <b>2002-1201</b> ④	100	 gray ④ <b>2002-1301</b> ④	100	 gray ④ <b>2002-1401</b> ④	100
 blue ④ <b>2002-1204</b> ④	100	 blue ④ <b>2002-1304</b> ④	100	 blue ④ <b>2002-1404</b> ④	100
 orange ④ <b>2002-1202</b> ④	100	 orange ④ <b>2002-1302</b> ④	100	 orange ④ <b>2002-1402</b> ④	100
 red ④ <b>2002-1203</b> ④	100	 red ④ <b>2002-1303</b> ④	100	 red ④ <b>2002-1403</b> ④	100
 black ④ <b>2002-1205</b> ④	100	 black ④ <b>2002-1305</b> ④	100	 black ④ <b>2002-1405</b> ④	100
 yellow ④ <b>2002-1206</b> ④	100	 yellow ④ <b>2002-1306</b> ④	100	 yellow ④ <b>2002-1406</b> ④	100
2-conductor ground terminal block		3-conductor ground terminal block		4-conductor ground terminal block	
 green-yellow ④ <b>2002-1207</b> ④	100	 green-yellow ④ <b>2002-1307</b> ④	100	 green-yellow ④ <b>2002-1407</b> ④	100
2-conductor shield terminal block		3-conductor shield terminal block		4-conductor shield terminal block	
 white <b>2002-1208</b>	100	 white <b>2002-1308</b>	100	 white <b>2002-1408</b>	100
Other terminal blocks with the same profile:		Other terminal blocks with the same profile:		Other terminal blocks with the same profile:	
Diode <b>2002-1211/1000-411</b> Page 112		Diode <b>2002-1311/1000-411</b> Page 112		Diode <b>2002-1411/1000-411</b> Page 112	
		LED <b>2002-1321/1000-434</b> Page 112		LED <b>2002-1421/1000-434</b> Page 112	
				Double-potential <b>2002-1441</b> Page 33	
Item-Specific Accessories		Item-Specific Accessories		Item-Specific Accessories	
End and intermediate plate, 0.8 mm thick		End and intermediate plate, 0.8 mm thick		End and intermediate plate, 0.8 mm thick	
 orange <b>2002-1292</b> 100 (4x25)		 orange <b>2002-1392</b> 100 (4x25)		 orange <b>2002-1492</b> 100 (4x25)	
 gray <b>2002-1291</b> 100 (4x25)		 gray <b>2002-1391</b> 100 (4x25)		 gray <b>2002-1491</b> 100 (4x25)	
Separator, oversized, 2 mm thick		Separator, oversized, 2 mm thick		Separator, oversized, 2 mm thick	
 orange <b>2002-1294</b> 100 (4x25)		 orange <b>2002-1394</b> 100 (4x25)		 orange <b>2002-1494</b> 100 (4x25)	
 gray <b>2002-1293</b> 100 (4x25)		 gray <b>2002-1393</b> 100 (4x25)		 gray <b>2002-1493</b> 100 (4x25)	
Separator for Ex e/Ex i applications, orange, 3 mm thick		Separator for Ex e/Ex i applications, orange, 3 mm thick		Separator for Ex e/Ex i applications, orange, 3 mm thick	
 90 mm <b>209-190</b> 50 (2x25)		 120 mm <b>209-191</b> 50 (2x25)		 120 mm <b>209-191</b> 50 (2x25)	
 120 mm <b>209-191</b> 50 (2x25)					

#### 2002 Series Accessories

Appropriate marking systems: WMB/WMB Inline/Marking strips  
(see Section 13)

Insulation stop, 5 pcs/strip, 0.25 ... 0.5 mm <sup>2</sup>	Push-in type jumper bar, insulated, I <sub>N</sub> 25 A, light gray	Push-in type jumper bar, insulated, I <sub>N</sub> 25 A, light gray
 light gray <b>2002-171</b> 200 (8x25)	 2-way <b>2002-402</b> 200 (8x25)	 from 1 to 3 <b>2002-433</b> 200 (8x25)
Insulation stop, 5 pcs/strip, 0.75 ... 1 mm <sup>2</sup>	 3-way <b>2002-403</b> 200 (8x25)	 from 1 to 4 <b>2002-434</b> 200 (8x25)
 dark gray <b>2002-172</b> 200 (8x25)	 4-way <b>2002-404</b> 200 (8x25)	 from 1 to 5 <b>2002-435</b> 100 (4x25)
Protective warning marker, with black high-voltage symbol, for 5 terminal blocks	 5-way <b>2002-405</b> 100 (4x25)	 from 1 to 6 <b>2002-436</b> 100 (4x25)
 yellow <b>2002-115</b> 100 (4x25)	 6-way <b>2002-406</b> 100 (4x25)	 from 1 to 7 <b>2002-437</b> 100 (4x25)
	 7-way <b>2002-407</b> 100 (4x25)	 from 1 to 8 <b>2002-438</b> 100 (4x25)
	 8-way <b>2002-408</b> 100 (4x25)	 from 1 to 9 <b>2002-439</b> 100 (4x25)
	 9-way <b>2002-409</b> 100 (4x25)	 from 1 to 10 <b>2002-440</b> 100 (4x25)
	 10-way <b>2002-410</b> 100 (4x25)	