



BALL BEARINGS


BORE SIZE	TYPE	MATERIAL
3/64" TO 1/2"	SINGLE ROW - FLANGED PRECISION ABEC-3 AND ABEC-7	440C STAINLESS STEEL



Shielded
Grease Per Mil-G-23827



Shielded
Oil Per Mil-L-6085



Unshielded
Oil Per Mil-L-6085



ABEC-3 STOCK NO.	ABEC-7 STOCK NO.	d	D	w	A	SHIELD DATA	E	DYNAMIC LOAD (LBS.)	STATIC LOAD (LBS.)
B2-16-Q3 B2-16-S-Q3	B2-16 B2-16-S	.0469	.1562	.0625 .0937	.203	UNSHIELDED SHIELDED	.013 .031	17	6
B2-17-Q3 B2-17-S-Q3	B2-17 B2-17-S	.0550	.1875	.0781 .1094	.234	UNSHIELDED SHIELDED	.023 .031	26	9
B2-12-Q3 B2-12-S-Q3	B2-12 B2-12-S	.0781	.2500	.0937 .1406	.296	UNSHIELDED SHIELDED	.023 .031	36	14
B2-13-Q3 B2-13-S-Q3	B2-13 B2-13-S	.0937	.3125	.1094 .1406	.359	UNSHIELDED SHIELDED	.023 .031	60	24
B2-14-Q3 B2-14-S-Q3	B2-14 B2-14-S	.1250	.2500	.0937 .1094	.296	UNSHIELDED SHIELDED	.023 .031	33	13
B2-15-Q3 B2-15-S-Q3	B2-15 B2-15-S		.3125	.1094 .1406	.359	UNSHIELDED SHIELDED	.023 .031	60	24
B2-5-Q3 B2-5-S-Q3	B2-5 B2-5-S		.3750	.1562 .1562	.440	UNSHIELDED SHIELDED	.030 .030	68	28
B2-20-Q3 B2-20-S-Q3	B2-20 B2-20-S	.1562	.3125	.1094 .1250	.359	UNSHIELDED SHIELDED	.023 .036	33	14
B2-18-Q3 B2-18-S-Q3	B2-18 B2-18-S	.1875	.3125	.1094 .1250	.359	UNSHIELDED SHIELDED	.023 .036	33	14
B2-9-Q3 B2-9-S-Q3	B2-9 B2-9-S		.3750	.1250 .1250	.422	UNSHIELDED SHIELDED	.023 .031	76	33
B2-6-Q3 B2-6-S-Q3	B2-6 B2-6-S		.5000	.1960 .1960	.565	UNSHIELDED SHIELDED	.042 .042	141	67
B2-10-Q3 B2-10-S-Q3	B2-10 B2-10-S	.2500	.3750	.1250 .1250	.422	UNSHIELDED SHIELDED	.023 .036	37	17
B2-11-Q3 B2-11-S-Q3	B2-11 B2-11-S		.5000	.1250 .1875	.547	UNSHIELDED SHIELDED	.023 .045	114	57
B2-7-Q3 B2-7-S-Q3	B2-7 B2-7-S		.6250	.1960 .1960	.690	UNSHIELDED SHIELDED	.042 .042	158	78
B2-21-Q3 B2-21-S-Q3	B2-21 B2-21-S	.3125	.5000	.1562 .1562	.547	UNSHIELDED SHIELDED	.031 .031	56	31
B2-8-Q3 B2-8-S-Q3	B2-8 B2-8-S	.3750	.8750	.2812 .2812	.969	UNSHIELDED SHIELDED	.062 .062	356	176
B2-22-S-Q3	B2-22-S	.5000	1.1250	.3125	1.225	SHIELDED	.062	827	464

See Section K (Reference Section) for Bearing Tolerances.